


GNSS

TE Internal #: 2108912-1

GNSS, Antenna, GNSS, Adhesive, Printed Circuit Board, Cable Assembly, MHF, Cable Length 2.166 in [55 mm], GNSS - Global - L1 - 1575.4, Embedded

[View on TE.com >](#)

Antennas

Wireless Application: **GNSS**Mounts To: **Printed Circuit Board**Mounting Retention Type: **Adhesive**Antenna Connection Type: **Cable Assembly**Antenna Connector Type: **MHF**

Features

Product Type Features

Antenna Connection Type	Cable Assembly
Antenna Connector Type	MHF

Configuration Features

Band Type	Single Band
Antenna Protocol	GNSS
Number of Ports	1
Antenna Style	Embedded

Electrical Characteristics

VSWR (Max)	< 2.0:1
Impedance	50 Ω
Active Antenna	Yes

Signal Characteristics

Frequency Band	1575.42 MHz
Gain (Max)	11.1 dB



Body Features

Product Weight	2.5 g[.08819 oz]
----------------	------------------

Mechanical Attachment

Region	Global
Polarization	RHCP
Mounts To	Printed Circuit Board
Mounting Retention Type	Adhesive

Dimensions

Cable Insulation Diameter (Max)	1.13 mm[.045 in]
Cable Length	55 mm[2.166 in]
Product Length	12 mm[.473 in]
Product Width	12 mm[.473 in]
Product Height	5.2 mm[.205 in]

Usage Conditions

Application by Region	GNSS - Global - L1 - 1575.4
-----------------------	-----------------------------

Operation/Application

Wireless Standard	L1/GPS Glonass Galileo
-------------------	------------------------

Industry Standards

Wireless Application	GNSS
----------------------	------

Packaging Features

Packaging Method	Tray/Box
------------------	----------

Other

Precision Level	Standard
-----------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219)



Candidate List Declared Against: JAN 2021 (211)

SVHC > Threshold:

Pb (3.7% in Component part)

2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (3% in Component part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | GNSS



Customers Also Bought



TE Part #878513-000
Bulbous Heat Shrink Boots: Lipped,
Right Angle



TE Part #154717-6
PL 250 REC TERMINAL 14-11 AWG
PTPB



TE Part #1-1703543-0
2POS,TAB 2.8X0.8,TAB HSG,ASSY

Documents

Product Drawings

[Active ant.,MHF,55mm,L1](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2108912-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108912-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108912-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Active ant.,MHF,55mm,L1](#)

English