

4.9 GHz to 5.8 GHz 27 dBi Lightweight Die-cast  
Grid Antenna Type N Female Connector

**HG4927EG-1-NF**



**Features**

- All weather operation
- Easy to assemble
- UV stable powder coat finish
- Die-cast aluminum construction
- High Gain

**Applications**

- 5 GHz ISM applications
- Long-range Directional Applications
- 5 GHz UNII applications
- Point to Point (PtP) and Multipoint to Point (MPtP)
- 5 GHz Wireless LAN system

**Description**

The L-com HG4927EG-1-NF is a high-performance light weight reflector grid antenna specifically designed for long-range directional point to point systems, point to multipoint and wireless bridges. L-com’s HG4927EG-1-NF has 25 to 27 dBi gain. The HG4927EG-1-NF operates from 4900 to 5850 MHz which is ideal for WLAN backhaul.

The HG4927EG-1-NF from L-com has 9° Vertical and 6° Horizontal Beamwidth patterns with vertical or horizontal polarization and features Type N female connectors. The 4900-5850 MHz HG4927EG-1-NF is shipped as a 2-piece reflector grid which is simple to assemble and greatly reduces shipping costs.

The Type N female connectorized HG4927EG-1-NF antenna from L-com has mounting bracket and hardware included which makes this antenna very easy to install. This high-performance light weight reflector grid antenna just like our wide selection of superior quality RF parts, ship same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

**Configuration**

Design	Grid
Polarization	Vertical
Connector Type	N Female

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	4.9		5.85	GHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		27		dBi
Front to Back Ratio	25			dB
Horizontal (Azimuth) HPBW		6		Degrees
Vertical (Elevation) HPBW		9		Degrees
Input Power			100	Watts

Click the following link (or enter part number in “SEARCH” on website) to obtain additional part information including price, inventory and certifications:  
[4.9 GHz to 5.8 GHz 27 dBi Lightweight Die-cast Grid Antenna Type N Female Connector HG4927EG-1-NF](#)

4.9 GHz to 5.8 GHz 27 dBi Lightweight Die-cast  
Grid Antenna Type N Female Connector

## HG4927EG-1-NF



### Mechanical Specifications

#### Size

Length	16.535 in [419.99 mm]
Width	24.803 in [630 mm]
Height	31 in [787.4 mm]
Mounting Mast Diameter	1.57 to 1.96 in [39.88 to 49.78 mm]
Weight	5.29109 lbs [2.4 kg]

### Environmental Specifications

#### Temperature

Operating Range	-40 to +70 deg C
Wind Survivability	124 MPH [199.56 KPH]
Humidity	5 to 95 %

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

4.9 GHz to 5.8 GHz 27 dBi Lightweight Die-cast Grid Antenna Type N Female Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# 4.9 GHz to 5.8 GHz 27 dBi Lightweight Die-cast Grid Antenna Type N Female Connector

## L-com CAD Drawing

