



TE Internal #: 2362375-4  
 PCI & PCI Express Connectors, Board-to-Board, 164 Position, 1 mm  
 Centerline, Vertical, Black, Height 11.25 mm, Width 8.8 mm, Printed  
 Circuit Board

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**  
 Number of Positions: **164**  
 PCI Generation: **4**  
 Centerline (Pitch): **1 mm**  
 Termination Post & Tail Length: **2.3 mm**

## Features

### Product Type Features

Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Positions	164
PCB Mount Orientation	Vertical

### Contact Features

Contact Current Rating (Max)	1.1 A
------------------------------	-------

### Termination Features

Termination Post & Tail Length	2.3 mm
--------------------------------	--------

### Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

### Housing Features

Centerline (Pitch)	1 mm
Housing Color	Black



### Dimensions

Connector Height	11.25 mm
Connector Width	8.8 mm

### Usage Conditions

Operating Temperature Range	-40 – 85 °C
-----------------------------	-------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

PCI Generation	4
----------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Customers Also Bought



## Documents

### Product Drawings

PCI-E GEN4, 164POS ,G/F ,DIP ,2.3mm TAIL

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2362375-4\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2362375-4\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2362375-4\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

2362375-4

PCI & PCI Express Connectors, Board-to-Board, 164 Position, 1 mm Centerline,  
Vertical, Black, Height 11.25 mm, Width 8.8 mm, Printed Circuit Board



## Product Specifications

### Product Specification

English