



GCQ15-KIT-R10-5R0-A-DE

**0402 Class1 Hi-Q Capacitor
Automotive AEC-Q200 Qualified**

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GCQ1555C1HR10WB01	1005M/0402	COG	50Vdc	0.1pF	±0.05pF	0.55max	20
2	GCQ1555C1HR20WB01	1005M/0402	COG	50Vdc	0.2pF	±0.05pF	0.55max	20
3	GCQ1555C1HR30WB01	1005M/0402	COG	50Vdc	0.3pF	±0.05pF	0.55max	20
4	GCQ1555C1HR40WB01	1005M/0402	COG	50Vdc	0.4pF	±0.05pF	0.55max	20
5	GCQ1555C1HR50WB01	1005M/0402	COG	50Vdc	0.5pF	±0.05pF	0.55max	20
6	GCQ1555C1HR60WB01	1005M/0402	COG	50Vdc	0.6pF	±0.05pF	0.55max	20
7	GCQ1555C1HR70WB01	1005M/0402	COG	50Vdc	0.7pF	±0.05pF	0.55max	20
8	GCQ1555C1HR80WB01	1005M/0402	COG	50Vdc	0.8pF	±0.05pF	0.55max	20
9	GCQ1555C1HR90WB01	1005M/0402	COG	50Vdc	0.9pF	±0.05pF	0.55max	20
10	GCQ1555C1H1R0WB01	1005M/0402	COG	50Vdc	1.0pF	±0.05pF	0.55max	20
11	GCQ1555C1H1R1BB01	1005M/0402	COG	50Vdc	1.1pF	±0.1pF	0.55max	20
12	GCQ1555C1H1R2BB01	1005M/0402	COG	50Vdc	1.2pF	±0.1pF	0.55max	20
13	GCQ1555C1H1R3BB01	1005M/0402	COG	50Vdc	1.3pF	±0.1pF	0.55max	20
14	GCQ1555C1H1R4BB01	1005M/0402	COG	50Vdc	1.4pF	±0.1pF	0.55max	20
15	GCQ1555C1H1R5BB01	1005M/0402	COG	50Vdc	1.5pF	±0.1pF	0.55max	20
16	GCQ1555C1H1R6BB01	1005M/0402	COG	50Vdc	1.6pF	±0.1pF	0.55max	20
17	GCQ1555C1H1R7BB01	1005M/0402	COG	50Vdc	1.7pF	±0.1pF	0.55max	20
18	GCQ1555C1H1R8BB01	1005M/0402	COG	50Vdc	1.8pF	±0.1pF	0.55max	20
19	GCQ1555C1H1R9BB01	1005M/0402	COG	50Vdc	1.9pF	±0.1pF	0.55max	20
20	GCQ1555C1H2R0BB01	1005M/0402	COG	50Vdc	2.0pF	±0.1pF	0.55max	20
21	GCQ1555C1H2R1BB01	1005M/0402	COG	50Vdc	2.1pF	±0.1pF	0.55max	20
22	GCQ1555C1H2R2BB01	1005M/0402	COG	50Vdc	2.2pF	±0.1pF	0.55max	20
23	GCQ1555C1H2R3BB01	1005M/0402	COG	50Vdc	2.3pF	±0.1pF	0.55max	20
24	GCQ1555C1H2R4BB01	1005M/0402	COG	50Vdc	2.4pF	±0.1pF	0.55max	20
25	GCQ1555C1H2R5BB01	1005M/0402	COG	50Vdc	2.5pF	±0.1pF	0.55max	20
26	GCQ1555C1H2R6BB01	1005M/0402	COG	50Vdc	2.6pF	±0.1pF	0.55max	20
27	GCQ1555C1H2R7BB01	1005M/0402	COG	50Vdc	2.7pF	±0.1pF	0.55max	20
28	GCQ1555C1H2R8BB01	1005M/0402	COG	50Vdc	2.8pF	±0.1pF	0.55max	20
29	GCQ1555C1H2R9BB01	1005M/0402	COG	50Vdc	2.9pF	±0.1pF	0.55max	20
30	GCQ1555C1H3R0BB01	1005M/0402	COG	50Vdc	3.0pF	±0.1pF	0.55max	20
31	GCQ1555C1H3R1BB01	1005M/0402	COG	50Vdc	3.1pF	±0.1pF	0.55max	20
32	GCQ1555C1H3R2BB01	1005M/0402	COG	50Vdc	3.2pF	±0.1pF	0.55max	20
33	GCQ1555C1H3R3BB01	1005M/0402	COG	50Vdc	3.3pF	±0.1pF	0.55max	20

34	GCQ1555C1H3R4BB01	1005M/0402	COG	50Vdc	3.4pF	±0.1pF	0.55max	20
35	GCQ1555C1H3R5BB01	1005M/0402	COG	50Vdc	3.5pF	±0.1pF	0.55max	20
36	GCQ1555C1H3R6BB01	1005M/0402	COG	50Vdc	3.6pF	±0.1pF	0.55max	20
37	GCQ1555C1H3R7BB01	1005M/0402	COG	50Vdc	3.7pF	±0.1pF	0.55max	20
38	GCQ1555C1H3R8BB01	1005M/0402	COG	50Vdc	3.8pF	±0.1pF	0.55max	20
39	GCQ1555C1H3R9BB01	1005M/0402	COG	50Vdc	3.9pF	±0.1pF	0.55max	20
40	GCQ1555C1H4R0BB01	1005M/0402	COG	50Vdc	4.0pF	±0.1pF	0.55max	20
41	GCQ1555C1H4R1BB01	1005M/0402	COG	50Vdc	4.1pF	±0.1pF	0.55max	20
42	GCQ1555C1H4R2BB01	1005M/0402	COG	50Vdc	4.2pF	±0.1pF	0.55max	20
43	GCQ1555C1H4R3BB01	1005M/0402	COG	50Vdc	4.3pF	±0.1pF	0.55max	20
44	GCQ1555C1H4R4BB01	1005M/0402	COG	50Vdc	4.4pF	±0.1pF	0.55max	20
45	GCQ1555C1H4R5BB01	1005M/0402	COG	50Vdc	4.5pF	±0.1pF	0.55max	20
46	GCQ1555C1H4R6BB01	1005M/0402	COG	50Vdc	4.6pF	±0.1pF	0.55max	20
47	GCQ1555C1H4R7BB01	1005M/0402	COG	50Vdc	4.7pF	±0.1pF	0.55max	20
48	GCQ1555C1H4R8BB01	1005M/0402	COG	50Vdc	4.8pF	±0.1pF	0.55max	20
49	GCQ1555C1H4R9BB01	1005M/0402	COG	50Vdc	4.9pF	±0.1pF	0.55max	20
50	GCQ1555C1H5R0BB01	1005M/0402	COG	50Vdc	5.0pF	±0.1pF	0.55max	20