



- The exclusive two-piece design offers the lowest threading force in the industry
- Small head height permits more efficient use of space in compact areas
- Average 14% lighter than one-piece ties
- Excellent for critical applications such as aircraft design
- Releaseable for bundle modifications prior to tensioning and cutoff

Part Number:	SST4H-L0
Product Family:	<i>Sta-Strap</i> ® Cable Ties - Releasable - Weather Resistant Nylon 6.6
Product Line:	Two Piece Nylon Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Cable Tie, Releasable, 14.8", Light-Heavy cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	Yes
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	Yes
Length (In.):	14.8

Length (mm):	376
Width (In.):	.300
Width (mm):	7.6
CE Compliant:	Yes
Cross Section:	Light-Heavy
Head Height (In.):	.325
Head Height (mm):	8.3
Head Width (In.):	.460
Head Width (mm):	11.7
Locking Style:	Releasable
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	4.00
Max. Bundle Diameter (mm):	102
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	120
Min. Loop Tensile Strength (N):	534
Std. Pkg. UOM:	PK
Thickness (In.):	.067
Thickness (mm):	1.7

Tool: GTH, GS4H, GS4EH, PTH, STH2, ST3EH

UOM: PC

Std. Pkg. Qty.: 50

Min. Order Qty.: 50