



## Contains

- 1 × Electronic Caliper: 150mm (6")
- 1 × Mechanical Micrometer: 0 to 25mm
- Housed in a fitted storage case

## Electronic Caliper




## Features

- Hardened stainless steel frame and measuring jaws
- Thumbroll adjustment
- Knurled locking screw
- Depth rod
- Clear LCD Display
- Large 11mm digits
- Inch/Metric conversion
- Origin setting
- 4 Way measurement
- Individual serial numbers
- Power: 1 x Silver oxide battery SR44 - 1.55v

## Specifications

Range	: 150mm (6")
Resolution	: 0.01mm (0.0005")
Repeatability	: 0.01mm (0.0005")
Accuracy	: ±0.03mm
Ext. Jaw Length	: 40mm
Int. Jaw Length	: 18mm
Operating Temperature	: +5°C to 40°C
Relative humidity	: 80% (Max.)



1. Metric / Inch Conversion Button
2. Knurled Locking Screw
3. LCD Display
4. Depth Measuring Blade
5. Caliper Beam
6. Thumbroll Fine Adjustment
7. Battery Cover
8. Zero Set Button
9. Power Button ON/OFF
10. External Measuring Jaws
11. Step Measuring Faces
12. Internal Measuring Jaws



## Mechanical Micrometers



### Features

- Accuracy conforms to DIN 863
- Accuracy is 0.004mm
- Resolution: 0.01mm (0.0001")
- Models above 25mm (1") supplied with setting rod
- Micro fine graduations for accurate reading
- Tungsten carbide measuring faces
- Spindle locking lever
- Style A
- Ratchet stop
- Non-glare satin chrome barrel and sleeve
- Blue baked enamel hammer tone finish
- Supplied in fitted case with adjustment tools

### Diagram



- |                        |                     |
|------------------------|---------------------|
| 1 Heat Resistant Plate | 9 Taper             |
| 2 Frame                | 10 End Cap          |
| 3 Anvil                | 11 Ratchet Stop     |
| 4 Spindle              | 12 Spanner          |
| 5 Spindle Lock         | 13 Setting Standard |
| 6 Sleeve               |                     |
| 7 Thimble              |                     |
| 8 Barrel               |                     |

### Part Number Table

Description	Part Number
Digital Caliper and Mechanical Micrometer Set	50-100-900

Dimensions : Millimetres

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of Premier Farnell Limited 2019.