

PRO-ELEC



Solar Road Stud Light Model: PEL01350

Please read these instructions carefully before use and retain for future reference.

IMPORTANT SAFETY INFORMATION

- Avoid locations of high temperature or humidity.
- The lamp is constructed to IP65 suitable for outdoor use.

WHAT'S INCLUDED

- Lamp assembly.
- User manual.

INSTALLATION

- The road stud can be either bolted to the surface or affixed using epoxy adhesive.
- Ensure the surface and the base of the stud are clean before applying adhesive. Allow at least 8 hours for the adhesive to cure fully.

OPERATION

- **Allow at least 8hrs for the battery to fully charge initially.**

NOTE: the lamp does not light except in low ambient light levels.

- When the ambient light falls below a preset level the LEDs will illuminate constantly.

CLEANING & MAINTENANCE

- Clean the unit only with a damp cloth. Do not use any chemicals, abrasives or solvents that could damage the casing or lens.

SPECIFICATION

Solar panel: 2V, 0.25W

Battery: 1 x Ni-MH 700mAh rechargeable.

LED: 6 Epistar white

Working time: up to 72 hours.

Dimensions: L105 x W95 x H23mm.

Load bearing: 20 tons.



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China
PO Box 13362 Dublin 2
PR2 9PP
Man Rev 1.2