

# PRO-ELEC



## Solar Path Spotlight Model: PEL01351

Please read these instructions carefully before use and retain for future reference.

### IMPORTANT SAFETY INFORMATION

- Avoid locations of high temperature or humidity.
- The lamp is constructed to IP65 suitable for outdoor use.

### WHAT'S INCLUDED

- Lamp assembly.
- User manual.

### INSTALLATION

- Installation is simply embedding the spike in the ground ensuring the solar panel is exposed for maximum charging efficiency but not in the vicinity of other strong light source or the low light illumination may not function.
- Turn the on/off switch under the top part to the ON position after locating.

### OPERATION

- **Allow at least 8hrs for the battery to fully charge initially.**
- NOTE:** the lamp does not light except in low ambient light levels.
- When the ambient light falls below a preset level the LEDs will illuminate constantly.

### CLEANING & MAINTENANCE

- Clean the unit only with a damp cloth. Do not use any chemicals, abrasives or solvents that could damage the casing or lens.

- During periods where the lamp may not be used, it is advisable to charge the battery occasionally to maintain its performance and before re-using the lamp.

## **SPECIFICATION**

Solar panel: Monocrystal 2V, 0.25W

Battery: 1 x Ni-MH 600mAh rechargeable.

LED: 1 x white FT8mm

Working time: up to 10 hours.

Dimensions: DIA100 x H370mm.



### **INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.**

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China  
PO Box 13362 Dublin 2  
PR2 9PP  
Man Rev 1.2