

## SPE PCB connector - SPE-T1-M8MSM-180-SMD - 1215777

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




SPE PCB connector, type: IEC 63171-5, degree of protection: IP65/IP67, number of positions: 2, CAT B (ISO/IEC 63171), connection method: Solder connection, Single Pair Ethernet

### Your advantages

- ✓ Compact design for maximum space savings
- ✓ Compatible with standard M8 housing screw connections
- ✓ Connectors in accordance with IEC 63171-5
- ✓ Data transmission up to 600 MHz



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 063151 297015
GTIN	4063151297015
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Dimensions

Width	10.1 mm
Height	22.1 mm
Length	14.5 mm

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 85 °C
-----------------------------------------	------------------

# SPE PCB connector - SPE-T1-M8MSM-180-SMD - 1215777

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP65/IP67 (in combination with M8 housing screw connection)

### General

Number of positions	2
Insulation resistance	> 1 TΩ
Overvoltage category	I
Degree of pollution	2
Connection method	Solder connection
Transmission characteristics (category)	CAT B (ISO/IEC 63171)
Halogen-free	yes
Resistance to oil	yes
Flame resistance	UL 94 V0
Locking type	Screw locking
Rated voltage (III/2)	72 V DC
Rated current	4 A

### Material

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	LCP

### Cable

Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	2250 V DC
Flame resistance	UL 94 V0
Halogen-free	yes
Resistance to oil	yes

### Standards and Regulations

Flame resistance	UL 94 V0
Resistance to oil	yes
Halogen-free	yes
Flammability rating according to UL 94	V0

## SPE PCB connector - SPE-T1-M8MSM-180-SMD - 1215777

### Classifications

eCl@ss

eCl@ss 10.0.1	27440390
eCl@ss 11.0	27440390
eCl@ss 9.0	27440402

### Accessories

#### Accessories

#### Panel mounting base

Housing screw connection - SACC-FP-M-M8/M10 SMD - 1412502



M8 pin, front mounting SMD with M10 screw fastening

---

Housing screw connection - SACC-BP-M-M8/M12 SMD - 1412505



M8 pin, rear mounting