

## Araldite® 2015-1

### Two Component Epoxy Paste Adhesive

#### Product Description

Araldite® 2015-1 is a two component, room temperature curing paste adhesive giving a resilient bond. It is thixotropic and non-sagging up to 10mm thickness. It is particularly suitable for SMC and GRP bonding.

#### Key Features

- Toughened Paste
- Ideal for bonding GRP, SMC and dissimilar substrates
- Gap filling, non-sagging up to 10mm thickness
- Good resistance to weathering

#### Typical Properties

Property	Araldite 2013-1 A (Resin)	Araldite 2013-1 B (Hardener)	A/B Mixed	Test Method
Color	Gray soft paste	Beige soft paste	Gray paste	Visual
Specific Gravity	1.4	1.4	1.4	ASTM D-1475
Viscosity at 77F, cP	thixotropic	thixotropic	thixotropic	ASTM D-2196
Pot Life (100g at 25°C), minutes			45-55	--
Mix Ratio by volume	100	100		--
Mix Ratio by weight	100	100		--

#### Typical Cured Properties

Unless otherwise stated, the figures given below were all determined by testing standard specimens made by lap-bonding 5" x 1"x 0.003" strips of primed aluminum panel. The joint area was 1" x 0.5" in each case.

The figures were determined with typical production batches using standard testing methods. They are provided solely as technical information and do not constitute a production specification.

# Advanced Materials

## Technical Datasheet

### Average handling shear strengths of typical primed aluminum to primed aluminum bonds.

Panels degreased with IPA, cured and tested at 25°C (77°F).

Time	Lap Shear Strength (psi)	Test Method
4 hours	>150	ASTM D-1002
6.5 hours	>1500	ASTM D-1002

### Average lap shear strengths of typical metal to metal joints.

Panels degreased with IPA, cured 24 hours at 25°C (77°F) and tested at 25°C (77°F).

Substrate	Lap Shear Strength (psi)	Test Method
Treated steel	2390	ASTM D-1002
Stainless steel	2720	ASTM D-1002
Primed aluminum	2640	ASTM D-1002

### Average lap shear strengths of typical plastic to plastic joints.

Panels lightly abraded and degreased with IPA, cured 7 days at 25°C (77°F) and tested at 25°C (77°F).

Substrate	Lap Shear Strength (psi)	Test Method
ABS	240	ASTM D-1002
PVC	370	ASTM D-1002
PC	520	ASTM D-1002
PMMA	250	ASTM D-1002

### Average lap shear strength versus tropical weathering (40°C/92% RH).

On primed aluminum panels. Panels degreased with IPA, cured 24 hours at 25°C (77°F) and tested at 25°C (77°F).

Time	Lap Shear Strength (psi)	Test Method
Initial LSS	2640	ASTM D-1002
After 30 days	3080	ASTM D-1002
After 60 days	3060	ASTM D-1002
After 90 days	3280	ASTM D-1002

# Advanced Materials

## Technical Datasheet

### Average lap shear strength versus immersion in various media.

On primed aluminum panels. Panels degreased with IPA cured 24 hours at 25°C (77°F) and tested at 25°C (77°F), test method ASTM D-1002.

Time	25°C	Gasoline	10% Acetic Acid	Xylene	25°C Water	70°C Water
Initial cure (25°C, 24 hours)	2640	2640	2640	2640	2640	2640
After 30 days, psi	2810	960	1880	2070	2680	1750
After 60 days, psi	2910	860	1610	2040	2840	1800
After 90 days, psi	3095	974	837	2090	2850	1670

### Average lap shear strength versus heat aging (70°C).

On primed aluminum panels. Panels degreased with IPA, cured 24 hours at 25°C (77°F) before aging and tested at 25°C (77°F).

Time	Lap Shear Strength (psi)	Test Method
Initial LSS	2640	ASTM D-1002
After 30 days	2980	ASTM D-1002
After 60 days	3370	ASTM D-1002
After 90 days	3360	ASTM D-1002

### Glass transition temperature (typical average values)

Cure: 80°C for 1 hour : 77°C by DMA

### DMA Shear Modulus G' (ISO 6721) (typical average values)

Cure: 1 hour at 80°C

-50°C: 1.8 GPa  
 0°C: 1 GPa  
 20°C: 900 MPa  
 50°C: 540 MPa  
 75°C: 61 MPa  
 100°C: 12 MPa

# Advanced Materials

## Technical Datasheet

### Flexural Properties (ISO 178) (typical average values)

Cure 16 hours at 40°C, tested at 23°C

Flexural Strength: 43 MPa

Flexural Modulus: 1800 MPa

### Tensile Properties (ISO 527) (typical average values)

Cure 16 hours at 40°C, tested at 23°C

Tensile Strength: 31 MPa

Tensile Modulus: 1600 MPa

Elongation at break: 4.2%

## Processing

### Pre-treatment

The strength and durability of the adhesive bond are dependent on proper treatment of the surfaces to be bonded. At the very least, the surfaces should be cleaned with an effective degreasing agent such as acetone or other proprietary degreasing agents in order to remove all traces of oil, grease, dirt and other surface contaminants.

Low Grade alcohol, gasoline (petrol) or paint thinners must never be used.

The strongest and most durable bonded assemblies are obtained by either mechanically abrading or chemically etching (“pickling”) the degreased surfaces. Mechanical abrading should be followed by a second degreasing treatment.

### Application of adhesive

The resin/hardener mix is applied manually or robotically to the pre-treated and dry joint surfaces. Huntsman’s technical support group can assist the user in the selection of a suitable application method as well as suggest a variety of reputable companies that manufacture and service adhesive dispensing equipment.

A layer of adhesive 0.002 to 0.004-inches (0.05 to 0.10-mm) thick will normally impart the greatest lap shear strength to a joint. It should also be noted that bonded assembly design also critical in providing a durable bond. The components to be bonded together should be assembled and maintained in a fixed position as soon as the adhesive has been applied. For more detailed explanations regarding surface preparations and pre-treatment, assembly design, and the twin cartridge dispensing system, visit [www.aralditeadhesives.com](http://www.aralditeadhesives.com)

### Equipment maintenance

All tools should be cleaned with hot soapy water before the adhesive has cured. If solvents such as acetone are used for cleaning, operators should take all the necessary precautions in order to prevent eyes or skin contact.

## Technical Datasheet

### Storage

Araldite 2015-1/A and Araldite 2015-1/B must be stored at room temperature and the components must be stored in sealed containers. The expiry date is indicated on the label.

### Precautionary Statement

Our products are generally quite harmless to handle provided that certain precautions normally taken when handling chemicals are observed. The uncured materials must not, for instance, be allowed to come in contact with foodstuffs or food utensils, and measures should be taken to prevent the uncured materials from coming in contact with the skin, since people with particularly sensitive skin may be affected. The wearing of impervious rubber or plastic gloves will normally be necessary; likewise, the use of eye protection. The skin should be thoroughly cleansed at the end of each working period by washing with soap and warm water. The use of solvents is to be avoided. Disposable paper- not cloth towels- should be used to dry the skin. Adequate ventilation of the working area is recommended. These precautions are described in greater detail in the Safety Data sheets for the individual products and should be referred to for fuller information.

### First Aid!

Refer to SDS as mentioned above.

**KEEP OUT OF REACH OF CHILDREN**

**FOR PROFESSIONAL AND INDUSTRIAL USE ONLY**

### Important Legal Notice

Sales of the product described herein ("Product") are subject to the general terms and conditions of sale of either Huntsman Advanced Materials LLC, or its appropriate affiliate including without limitation Huntsman Advanced Materials (Europe) BVBA, Huntsman Advanced Materials Americas Inc., or Huntsman Advanced Materials (Hong Kong) Ltd. ("Huntsman"). The following supersedes Buyer's documents.

Huntsman warrants that at the time and place of delivery all Products sold to Buyer shall conform to the specifications provided to Buyer by Huntsman.

While the information and recommendations included in this publication are, to the best of Huntsman's knowledge, accurate as of the date of publication, NOTHING CONTAINED HEREIN (EXCEPT AS SET FORTH ABOVE REGARDING CONFORMANCE WITH SPECIFICATIONS PROVIDED TO BUYER BY HUNTSMAN) IS TO BE CONSTRUED AS A REPRESENTATION OR WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, NONINFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHTS, OR WARRANTIES AS TO QUALITY OR CORRESPONDENCE WITH PRIOR DESCRIPTION OR SAMPLE, AND THE BUYER ASSUMES ALL RISK AND LIABILITY WHATSOEVER RESULTING FROM THE USE OF SUCH PRODUCT, WHETHER USED SINGLY OR IN COMBINATION WITH OTHER SUBSTANCES.

# Advanced Materials

## Technical Datasheet

No statements or recommendations made herein are to be construed as a representation about the suitability of any Product for the particular application of Buyer or user or as an inducement to infringe any patent or other intellectual property right. Buyer is responsible to determine the applicability of such information and recommendations and the suitability of any Product for its own particular purpose, and to ensure that its intended use of the Product does not infringe any intellectual property rights.

The Product may be or become hazardous. The Buyer should obtain Material Safety Data Sheets and Technical Data Sheets from Huntsman containing detailed information on Product hazards and toxicity, together with proper shipping, handling and storage procedures for the Product, and should comply with all applicable governmental laws, regulations and standards relating to the handling, use, storage, distribution and disposal of, and exposure to the Product. Buyer shall also take all steps necessary to adequately inform, warn and familiarize its employees, agents, direct and indirect customers and contractors who may handle or be exposed to the Product of all hazards pertaining to and proper procedures for safe handling, use, storage, transportation and disposal of and exposure to the Product, and the containers or equipment in which the Product may be handled, shipped or stored.

Araldite® is a registered trademark of Huntsman LLC or an affiliate thereof in one or more, but not all countries.

© 2015 Huntsman Advanced Materials Inc.

### Main Offices:

#### **Huntsman Corporation**

10003 Woodloch Forest Dr.  
The Woodlands, TX 77380  
888-564-9318

#### **Huntsman Advanced Technology Center**

8600 Gosling Rd.  
The Woodlands, TX 77381  
281-719-7400