

## Product information

# 34 22 130

## Precision Electronics Gripping Pliers

DIN ISO 9655



- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Smoothly ground gripping surfaces, edges finely rounded
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Half-round jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened




### General

Article No.	34 22 130
EAN	4003773061472
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	135 x 59 x 19 mm
Standard	DIN ISO 9655
Reach	no
RohS	no

### Technical details

Jaw length (B)	22.7 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.6 mm
Tips thickness (F)	1.6 mm
Head width (A)	11.2 mm



<b>Classification</b>	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

*technical change and errors excepted*

