

Product information

34 22 130 ESD

Precision Electronics Gripping Pliers ESD

DIN ISO 9655 DIN EN 61 340-5




- The assortment for highest standard of performance and results
- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Bolted joint: precise, zero backlash operation of pliers
- Precisely finished joint surfaces for smooth, low friction movement along the complete opening range
- Low-friction double spring for gentle and even opening
- Smooth ground gripping surfaces, edges carefully deburred
- Non-reflective finish
- Low weight
- Ergonomically shaped, two-colour dual component ESD handles, black/grey
- Half-round jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened



General	
Article No.	34 22 130 ESD
EAN	4003773061656
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	65 g
Dimensions	135 x 60 x 18 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
Reach	no
RohS	no

Technical details	
Jaw length (B)	22.7 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.6 mm
Tips thickness (F)	1.6 mm
Head width (A)	11.2 mm
ESD	yes





Classification	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted