MOSFET - Power, Single N-Channel, TOLL

80 V, 1.7 mΩ, 203 A

NTBLS1D7N08H

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Lowers Switching Noise/EMI
- These Devices are Pb-Free and are RoHS Compliant

Typical Applications

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	80	V
Gate-to-Source Voltage	Э		V _{GS}	±20	V
Continuous Drain		T _C = 25°C	I _D	203	Α
Current R _{θJC} (Notes 1, 3)	Steady	T _C = 100°C		143	
Power Dissipation	State	T _C = 25°C	P_{D}	167	W
R _{θJC} (Note 1)		T _C = 100°C		83	
Continuous Drain	T _A = 25°C		I _D	29	Α
Current R _{0JA} (Notes 1, 2, 3)	Steady	T _A = 100°C		21	
Power Dissipation	State T _A = 25°C		P_{D}	3.5	W
R _{θJA} (Notes 1, 2)		T _A = 100°C		1.7	
Pulsed Drain Current	$T_C = 25^{\circ}C, t_p = 100 \ \mu s$		I _{DM}	1173	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			Is	139	Α
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 27 A)			E _{AS}	1093.5	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			T _L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 1)	$R_{\theta JC}$	0.9	°C/W
Junction-to-Ambient - Steady State (Notes 1, 2)	$R_{\theta JA}$	43	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- 3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.



ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
80 V	1.7 mΩ @ 10 V	203 A



N-CHANNEL MOSFET



TOLL CASE 100CU

MARKING DIAGRAM



1D7N08H = Specific Device Code

A = Assembly Location

Y = Year

WW = Work Week

ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Cond	ition	Min	Тур	Max	Unit
OFF CHARACTERISTICS							•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D =	= 250 μA	80			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /				57		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V,	T _J = 25 °C			10	
		$V_{DS} = 80 \text{ V}$	T _J = 125°C			250	μΑ
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS}$	_S = 20 V			100	nA
ON CHARACTERISTICS							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D$	= 479 μΑ	2.0	2.9	4.0	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J	I _D = 479 μA, re	f to 25°C		-7.3		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 80 A		1.29	1.7	
		V _{GS} = 6 V	I _D = 43 A		1.76	2.6	mΩ
Forward Transconductance	9 _{FS}	$V_{DS} = 5 \text{ V}, I_{D}$	= 80 A		271		S
CHARGES, CAPACITANCES & GATE RE	SISTANCE						
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 40 V			7675		pF
Output Capacitance	C _{OSS}				1059		
Reverse Transfer Capacitance	C _{RSS}				41		
Gate-Resistance	R _G				0.6		
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 40 V; I _D = 80 A			121		nC
Threshold Gate Charge	Q _{G(TH)}				19		
Gate-to-Source Charge	Q _{GS}				32		
Gate-to-Drain Charge	Q_{GD}				29		
Plateau Voltage	V_{GP}				4.5		V
Output Charge	Q _{OSS}	V _{GS} = 0 V, V _{DD} = 40 V			149		nC
SWITCHING CHARACTERISTICS (Note 4	1)				•		•
Turn-On Delay Time	t _{d(ON)}				29		
Rise Time	t _r	V_{GS} = 10 V, V_{DS} = 40 V, I_{D} = 80 A, R_{G} = 6 Ω			25		1
Turn-Off Delay Time	t _{d(OFF)}				89		ns -
Fall Time	t _f				35		
DRAIN-SOURCE DIODE CHARACTERIS	STICS			-	-		-
Forward Diode Voltage	V _{SD}	$V_{GS} = 0 \text{ V}, \qquad T_{J} = 25^{\circ}\text{C}$			0.82	1.2	.,
		1 00 4	T _J = 125°C		0.69		V
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dIS/dt = 100 A/μs,			73		ns
Reverse Recovery Charge	Q _{RR}	$V_{GS} = 0 \text{ V, dis/di} = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 43 \text{ A}$			138		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

^{4.} Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On–Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source-to-Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS





Figure 7. Gate Charge Characteristics

Figure 8. Capacitance vs. Drain-to-Source Voltage







Figure 9. Drain Current vs. Case Temperature

Figure 10. Peak Power






Figure 11. Unclamped Inductive Switching Capability

Figure 12. Forward Bias Safe Operating Area

TYPICAL CHARACTERISTICS




Figure 13. Transient Thermal Impedance


DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NTBLS1D7N08H	1D7N08H	M0-299A (Pb-Free)	2000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

H-PSOF8L 11.68x9.80 CASE 100CU



E4 (2X)

E5 (2X)

_E6 (2X)

E8 [E9

BOTTOM VIEW

É7

DIM	MILLIMETERS			
5	MIN.	NOM.	MAX.	
Α	2.20	2.30	2.40	
A3	0.40	0.50	0.60	
b	0.70	0.80	0.90	
b1		8.00 REF	:	
С	0.40	0.50	0.60	
c1	0.10			
D	9.70	9.80	9.90	
D1	9.80	9.90	10.00	
D2		4.73 BSC	;	
D3		0.40 REF	=	
D4	:	3.75 BSC	;	
D5	_	1.20		
D6	7.40	7.50	7.60	
D7	(8.30)			
E	11.58	11.68	11.78	
E1	10.28	10.38	10.48	
E2	0.60	0.70	0.80	
E3		3.30 REF	:	
E4	— 2.60 —			

DIM	MILLIMETERS			
Divi	MIN. NOM. MAX		MAX.	
е		1.20 BSC		
e/2	(0.60 BSC	;	
e1		3.40 BSC	;	
K	1.50	1.57	1.70	
L	1.90	2.00	2.10	
L2	0.50	0.60	0.70	
Z	0.35 REF			
θ	0°		12°	
aaa	0.20			
bbb	0.25			
ccc		0.20		
ddd	0.20			
eee	0.10			
E5		3.30		
E6		0.65	_	
E7	7.15 REF			
E8	6.55 6.65 6.75		6.75	
E9	5.89 BSC			
E10	5.19 BSC			

13.28

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com TECHNICAL SUPPORT

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative