

## Product information

# 64 22 115

## Electronics End Cutting Nipper

DIN ISO 9654



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- End Cutter, mini-blade with small bevel
- Ball bearing chrome steel, oil hardened



### General

Article No.	64 22 115
EAN	4003773017806
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 69 x 18 mm
Standard	DIN ISO 9654
Reach	no
RohS	no


### Technical details

Cutting capacities soft wire (diameter)	Ø 0.8 mm
Head width (A)	11 mm
Jaw length (B)	20 mm
Jaw thickness (joint) (D)	6 mm
Cutting edge length mm (C)	3 mm

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004
UNSPSC 13.1	27112117

*technical change and errors excepted*



64 22 115

