

## TECHNICAL DATA SHEET

Part#: 5-TA

**Tweezers - 4 Star Straight Tapered Ultra Fine Point - Titanium Alloy**  
Ultimate tweezers for high power microscopy featuring extremely tapered tips for excellent visibility. - Solder will not adhere to tool - Light weight

The 5-TA titanium alloy tweezers are designed for high temperature applications (806°F (430°C)). They are also very light and have high resistance to most acids. They have zero magnetic retentivity and solder will not stick to them. They feature our hardest points.

• Precision Level	★★★★
• Material	Titanium Alloy
• Surface Resistivity	Conductive
• Shape	Straight Tapered
• Tip Size	.003" x .0025" (.075mm x .0625mm)
• Tip Angle	Straight
• Tip Length	
• Body Width	.375" (9.38mm)
• Body Height	.06" (1.5mm)
• OAL	4.25" (106.25mm)
• Weight (OZ)	1
• UPC	662847002779
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Titanium



C.T.M.  
Critical Tip Measurements  
(Tip Width and Thickness of one point)

