

TECHNICAL DATA SHEET

Part#: 15A-GW-ET

Tweezers - 3 Star Cutting - 15A-GW Series - Carbon Steel - Ergo
Designed for general purpose cutting of small wires or flashing. This tool is epoxy coated to prevent oxidation. - Ergonomic ESD grips for comfort

The 15A-GW-ET 70° angulated tip cutting tweezer is ideal for general purpose cutting of soft wire up to 0.010". This tool is considered a tip cutter in that the blades meet most predominately at the tip. All of the force applied to the tweezer gets transferred to the tips. It features our Ergo-Tweeze[®] soft cushioned Anti-Static grips (10¹⁰ ohms/sq surface resistivity), which also protect the user from heat.

• Precision Level	★★★
• Material	Carbon Steel
• Surface Resistivity	10 ¹⁰ ohms/sq
• Shape	Angulated
• Tip Size	.215" (5.38mm)
• Tip Angle	70°
• Tip Length	
• Body Width	0.75" (18.75mm)
• Body Height	1" (25mm)
• OAL	5" (125mm)
• Weight (OZ)	2
• UPC	662847003349
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Standard Head (15A-GW)

