

## TECHNICAL DATA SHEET

Part#: 54-MW

Tweezers - Cutting - 80°Angulated .122" Tip - Carbon Steel  
Designed for maximum visibility when working under magnification

The 54-MW 80°angled tip high precision micro cutting tweezer with ultra fine blades is designed for maximum visibility when working under magnification. It is coated with an epoxy coating ( $10^5$ - $10^6$  ohms/sq surface resistivity) to prevent oxidation.

• Precision Level	★★★
• Material	Carbon Steel
• Surface Resistivity	$10^5$ - $10^6$ ohms/sq
• Shape	Angled
• Tip Size	.122" (3.1mm)
• Tip Angle	80°
• Tip Length	.303" (7.7mm)
• Body Width	0.375" (9.38mm)
• Body Height	.06" (1.5mm)
• OAL	4.25" (106.25mm)
• Weight (OZ)	1
• UPC	662847004162
• Schedule B	8203.20.20.00
• ECCN	EAR99
• UNSPSC Code	27112105
• Country of Origin	Switzerland
• Group	Miniature Heads

