

## TECHNICAL DATA SHEET

Part#: 55-MW

Tweezers - Cutting - 40°Angulated .12" Tip - Carbon Steel  
Designed for maximum visibility when working under magnification

The 55-MW 40°angled tip high precision micro cutting tweezer is designed for maximum visibility when working under magnification. It is coated with an epoxy coating ( $10^5$ - $10^6$  ohms/sq surface resistivity) to prevent oxidation.

- Precision Level ★★★
- Material Carbon Steel
- Surface Resistivity  $10^5$ - $10^6$  ohms/sq
- Shape Angled
- Tip Size .12" (3mm)
- Tip Angle 40°
- Tip Length .157" (4mm)
- Body Width .291 (7.28mm)
- Body Height .06" (1.5mm)
- OAL 4.25" (106.25mm)
- Weight (OZ) 1
- UPC 662847004179
- Schedule B 8203.20.20.00
- ECCN EAR99
- UNSPSC Code 27112105
- Country of Origin Switzerland
- Group Miniature Heads

