


Integral Handle Probes with Custom Measurement Tips



Completely assembled with 0.3 m (1') retractable cable (stretches to 1.5 m [5']) and SMPW connector, shown smaller than actual size.

* Rated temperature is dependent on thermocouple type, sheath diameter and environment.

AVAILABLE FOR FAST DELIVERY!




4.5 mm ($\frac{3}{16}$ " OD

\$45

Tip designed for easy penetration into soft and semi-frozen objects. Made from rugged 304 stainless steel. Tip rated to 900°C (1650°F).

Penetration Probe
HPS-NP-[*]-316G-12



Reduced to
1.5 mm ($\frac{1}{16}$ " OD

\$50

Special small diameter ($\frac{1}{16}$ " tip designed for fast response. Made from 304 stainless steel. Tip rated to 900°C (1600°F).

Fast Response Probe
HPS-RT-[*]-18G-12




6.0 mm ($\frac{1}{4}$ " OD

\$75

Flexible tip which conforms to most surfaces for fast, repeatable, accurate measurements. Made from RTV silicone rubber for good thermal contact. Tip rated to 260°C (500°F). Warning: Subjecting sensor tip to temperatures above 316°C (600°F) will result in damage to tip.

Flexible Tip Surface Probe
HPS-FSP-[*]-14E-12



4.5 mm ($\frac{3}{16}$ " OD

\$85

Radiant energy shield with fine-gage wire thermocouple and 304 stainless steel sheath. Thermocouple tip is exposed to air flow for fast measurements, and the constant diameter design facilitates easy insertion into duct work, grilles and air vents. Tip rated to 870°C (1650°F)

Air Probe
HPS-AP-[*]-316E-12

* Insert thermocouple Type J, K, T, E or N



**Rugged!
High Impact
Plastic**

For RTDs
please see
page C-55.

Made from the same material as professional football helmets, these rugged probe handles have endurance designed in to provide long life.

70°C (160°F)
handle rating.

Custom Assemblies Available

Thermocouple probes with integral high impact plastic handles, with 300 mm (12") retractable cord with stripped leads (other terminations are available). Handles are rated to 70°C (160°F).


Probes shown are available in RTD, J, K, T and E calibrations. Other sheath and lead lengths are available. Consult Sales for details.

Integral Handle Probes

General Purpose Design



- ✓ Heavy Duty
- ✓ 300 mm (12") Probe Length Standard†
- ✓ 0.3 m (1') Color-Coded Retractable Cable Stretches to 1.5 m (5')
- ✓ Handle Rated to 70°C (160°F)
- ✓ Stainless Steel or Inconel Sheath
- ✓ SMP Molded Miniature Male Connector on Retractable Cable for Fast Hook-up to Instrumentation
- ✓ PFA Coating Available



Sensors and matching calibration handles.

For probe lengths over the maximum listed, consult quotations for special heavy duty construction probes.

Probe Dia. mm (in)	Max Length mm (in)
1.5 (1/16")	900 (36)
3.0 (3/16")	750 (30)
4.5 (3/16")	600 (24)
6.0 (1/4")	450 (18)

Discount Schedule	
1-10 UnitsNet
11-24 Unit10%
25-49 Units20%
50 and upConsult Sales

Note: Supplied with HDX aluminum handle for lengths over 600 mm (24"). Consult Sales for pricing. Cable termination with standard size connector available, see ordering example.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Thermocouple Alloy	Sheath Dia.	Grounded Junction	Price	Ungrounded Junction	Price	Exposed Junction	Price	Price/Add'l 300 mm (ft)
IRON-CONSTANTAN Inconel Sheath J	1.5 (1/16")	HPS-ICIN-116G-12-SMP-M	\$37	HPS-ICIN-116U-12-SMP-M	\$39	HPS-ICIN-116E-12-SMP-M	\$37	\$1.55
	3.0 (3/16")	HPS-ICIN-18G-12-SMP-M	37	HPS-ICIN-18U-12-SMP-M	39	HPS-ICIN-18E-12-SMP-M	37	3.15
	4.5 (3/16")	HPS-ICIN-316G-12-SMP-M	38	HPS-ICIN-316U-12-SMP-M	40	HPS-ICIN-316E-12-SMP-M	38	4.35
	6.0 (1/4")	HPS-ICIN-14G-12-SMP-M	41	HPS-ICIN-14U-12-SMP-M	43	HPS-ICIN-14E-12-SMP-M	41	7.50
IRON-CONSTANTAN 304SS Sheath J	1.5 (1/16")	HPS-ICSS-116G-12-SMP-M	\$37	HPS-ICSS-116U-12-SMP-M	\$39	HPS-ICSS-116E-12-SMP-M	\$37	\$1.55
	3.0 (3/16")	HPS-ICSS-18G-12-SMP-M	37	HPS-ICSS-18U-12-SMP-M	39	HPS-ICSS-18E-12-SMP-M	37	1.85
	4.5 (3/16")	HPS-ICSS-316G-12-SMP-M	38	HPS-ICSS-316U-12-SMP-M	40	HPS-ICSS-316E-12-SMP-M	38	3.15
	6.0 (1/4")	HPS-ICSS-14G-12-SMP-M	41	HPS-ICSS-14U-12-SMP-M	43	HPS-ICSS-14E-12-SMP-M	41	5.00
CHROMEGA®-ALOMEGA® Inconel Sheath K	1.5 (1/16")	HPS-CAIN-116G-12-SMP-M	\$37	HPS-CAIN-116U-12-SMP-M	\$39	HPS-CAIN-116E-12-SMP-M	\$37	\$1.55
	3.0 (3/16")	HPS-CAIN-18G-12-SMP-M	37	HPS-CAIN-18U-12-SMP-M	39	HPS-CAIN-18E-12-SMP-M	37	3.15
	4.5 (3/16")	HPS-CAIN-316G-12-SMP-M	38	HPS-CAIN-316U-12-SMP-M	40	HPS-CAIN-316E-12-SMP-M	38	4.35
	6.0 (1/4")	HPS-CAIN-14G-12-SMP-M	41	HPS-CAIN-14U-12-SMP-M	43	HPS-CAIN-14E-12-SMP-M	41	7.50
CHROMEGA®-ALOMEGA® 304SS Sheath K	1.5 (1/16")	HPS-CASS-116G-12-SMP-M	\$37	HPS-CASS-116U-12-SMP-M	\$39	HPS-CASS-116E-12-SMP-M	\$37	\$1.55
	3.0 (3/16")	HPS-CASS-18G-12-SMP-M	37	HPS-CASS-18U-12-SMP-M	39	HPS-CASS-18E-12-SMP-M	37	1.85
	4.5 (3/16")	HPS-CASS-316G-12-SMP-M	38	HPS-CASS-316U-12-SMP-M	40	HPS-CASS-316E-12-SMP-M	38	3.15
	6.0 (1/4")	HPS-CASS-14G-12-SMP-M	41	HPS-CASS-14U-12-SMP-M	43	HPS-CASS-14E-12-SMP-M	41	5.00
CHROMEGA®-CONSTANTAN Inconel Sheath E	1.5 (1/16")	HPS-CXIN-116G-12-SMP-M	\$37	HPS-CXIN-116U-12-SMP-M	\$39	HPS-CXIN-116E-12-SMP-M	\$37	\$1.85
	3.0 (3/16")	HPS-CXIN-18G-12-SMP-M	37	HPS-CXIN-18U-12-SMP-M	39	HPS-CXIN-18E-12-SMP-M	37	3.75
	4.5 (3/16")	HPS-CXIN-316G-12-SMP-M	38	HPS-CXIN-316U-12-SMP-M	40	HPS-CXIN-316E-12-SMP-M	38	5.00
	6.0 (1/4")	HPS-CXIN-14G-12-SMP-M	45	HPS-CXIN-14U-12-SMP-M	47	HPS-CXIN-14E-12-SMP-M	45	7.50
CHROMEGA®-CONSTANTAN 304SS Sheath E	1.5 (1/16")	HPS-CXSS-116G-12-SMP-M	\$37	HPS-CXSS-116U-12-SMP-M	\$39	HPS-CXSS-116E-12-SMP-M	\$37	\$1.55
	3.0 (3/16")	HPS-CXSS-18G-12-SMP-M	37	HPS-CXSS-18U-12-SMP-M	39	HPS-CXSS-18E-12-SMP-M	37	2.50
	4.5 (3/16")	HPS-CXSS-316G-12-SMP-M	38	HPS-CXSS-316U-12-SMP-M	40	HPS-CXSS-316E-12-SMP-M	38	3.15
	6.0 (1/4")	HPS-CXSS-14G-12-SMP-M	41	HPS-CXSS-14U-12-SMP-M	43	HPS-CXSS-14E-12-SMP-M	41	5.00
COPPER-CONSTANTAN Inconel Sheath T	1.5 (1/16")	HPS-CPIN-116G-12-SMP-M	\$37	HPS-CPIN-116U-12-SMP-M	\$39	HPS-CPIN-116E-12-SMP-M	\$37	\$1.85
	3.0 (3/16")	HPS-CPIN-18G-12-SMP-M	37	HPS-CPIN-18U-12-SMP-M	39	HPS-CPIN-18E-12-SMP-M	37	3.75
	4.5 (3/16")	HPS-CPIN-316G-12-SMP-M	38	HPS-CPIN-316U-12-SMP-M	40	HPS-CPIN-316E-12-SMP-M	38	5.00
	6.0 (1/4")	HPS-CPIN-14G-12-SMP-M	45	HPS-CPIN-14U-12-SMP-M	47	HPS-CPIN-14E-12-SMP-M	45	7.50
COPPER-CONSTANTAN 304SS Sheath T	1.5 (1/16")	HPS-CPSS-116G-12-SMP-M	\$37	HPS-CPSS-116U-12-SMP-M	\$39	HPS-CPSS-116E-12-SMP-M	\$37	\$1.55
	3.0 (3/16")	HPS-CPSS-18G-12-SMP-M	37	HPS-CPSS-18U-12-SMP-M	39	HPS-CPSS-18E-12-SMP-M	37	2.50
	4.5 (3/16")	HPS-CPSS-316G-12-SMP-M	38	HPS-CPSS-316U-12-SMP-M	40	HPS-CPSS-316E-12-SMP-M	38	3.15
	6.0 (1/4")	HPS-CPSS-14G-12-SMP-M	41	HPS-CPSS-14U-12-SMP-M	43	HPS-CPSS-14E-12-SMP-M	41	5.00

† Other lengths available, consult Sales department. For standard size "OSTW" connector add suffix "-OSTW" to model number and add \$5 to price. Ordering Example: HPS-CASS-14G-12-SMP-M, Type K probe, 1/16" diameter, 304SS sheath, SMP connector, grounded junction with miniature connector, \$41.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters