TE Internal #: 1SNL325060R0000

Power Distribution Blocks, Single Pole, 1 Pole, 250 A Current Rating

(UL), 7 Position, Wire & Cable, Power, DIN Rail / Panel Mount

View on TE.com >



Connectors > Terminal Blocks & Strips > Power Distribution Blocks



Number of Poles: 1

Circuit Configuration: Single Pole

Current Rating (IEC): 250 A

Current Rating (UL): 250 A

Number of Positions: 7

Features

Product Type Features

Sealable	No
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Poles - Main Circuit	1
Number of Poles - Output 1	6
Block Configuration	Feed-Through
Number of Levels	1
Number of Circuits	1
Number of Poles	1
Circuit Configuration	Single Pole
Number of Positions	7
Flectrical Characteristics	

Electrical Characteristics

Impulse Withstanding Voltage Rating (IEC)	8000 V
Power Loss	8 W
Short-Time Withstanding Current Rating @ 1s	11400 A
Voltage Rating (IEC)	1000 VAC
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	1000 V
Voltage Rating (CSA)	1000 V
Peak Withstanding Current Rating	23 kA



Dielectric Test Voltage	2200 V
Input Current (Max)	250 A
Current Rating (IEC)	250 A
Current Rating (UL)	250 A
Body Features	
Product Weight	224 g
Contact Features	
Contact Current Rating (Max)	250 A
Mechanical Attachment	
Tightening Torque - Output 1	18 – 26.5 in-lbs
Connection Type	Screw
Tightening Torque - Main Circuit	120 in-lbs
Connector Mounting Type	DIN Rail, Panel Mount
Housing Features	
Housing Material	Polyamide
Housing Color	Gray
Dimensions	
Output 1 Capacity - 1 Insulated Ferrule	14 – 6 AWG
Wire Stripping Length - Main Circuit	15 mm[.59 in]
Main Circuit Capacity - Flexible Bar	3 x 9 x 0.8 mm, 6 x 15.5 x 0.8 mm
Main Circuit Capacity - Solid Bar	12 x 4 mm
Hole Diameter - Output 1	6.7 mm[.26 in]
Output 1 Capacity - 1 Rigid Stranded Conductor	14 – 6 AWG
Input Dimensions - Main Circuit	15.5 x 7.2 mm[0.59 x 0.28 in]
Tool Size - Output 1	5.5 mm[.22 in]
Wire Stripping Length - Output 1	11 mm[.43 in]
Tool Size - Main Circuit	5 mm[.2 in]
Product Spacing	29 mm[1.14 in]
Rated Cross Section	6 mm ²
Product Depth	50.7 mm[2 in]
Product Width	29 mm[1.14 in]
Product Height	75 mm[2.95 in]



Usage Conditions

Storage Temperature Range	-55 – 110 °C[-67 – 230 °F]
Installation Temperature Range	-5 - 40 °C[23 - 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Operation/Application

Circuit Application Power	
---------------------------	--

Industry Standards

Tool - Output 1	Flat Screwdriver
Tool - Main Circuit	Allen Key
IP Rating	IP20
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach



Compatible Parts







Customers Also Bought





















Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNL325060R0000_A.2d_dxf.zip

English

Customer View Model



ENG_CVM_CVM_1SNL325060R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNL325060R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Datasheets & Catalog Pages

ENTRELEC DBL Power Distribution Blocks Catalogue

French

ENTRELEC DBL Power Distribution Blocks Catalogue

English

ENTRELEC Terminal Block - Master Catalog

English

DBL Power-Distribution-Blocks

English

Agency Approvals

CE Declaration of Conformity

English