





#### **Features**

- Universal 85 305V AC or 120 430V DC Input voltage
- Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range: -30°C to +70°C
- Low standby power consumption, high efficiency
- High I/O isolation test voltage up to 4000V AC
- · Low ripple & noise
- · Output short circuit, over-current, over-voltage protection
- IEC/EN/UL62368, EN60335, EN61558, GB4943 safety approved
- Over-voltage class III (designed to meet EN61558)
- · Operating altitude up to 5000m
- · 3 years warranty

MPM50-23Bxx series is an enclosed AC-DC switching power supply. It features universal AC input and at the same time accepts DC input voltage, cost-effective, low no load power consumption, high efficiency, high reliability and double or reinforced insulation. These converters offer excellent EMC performance and meet IEC/EN61000-4, CISPR32/EN55032, IEC/UL/EN62368, EN60335, EN61558, GB4943 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home etc.

Selection Guide								
Part Number	Output Power (W)	Nominal Output Voltage and Current (Vo/lo)	Output Voltage Adjustable Range (V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (µF)			
MPM50-23B05	50	5V/10A	4.5-5.5	83	8500			
MPM50-23B12	50.4	12V/4.2A	10.2-13.8	86	2000			
MPM50-23B15	51	15V/3.4A	13.5-18	87	1500			
MPM50-23B24	52.8	24V/2.2A	21.6-28.8	88	1000			
MPM50-23B48	52.8	48V/1.1A	43.2-52.8	90	220			

Input Specifications							
Item	Oper	ating Conditions	Min.	Тур.	Max.	Unit	
land Valtana Dana	AC input		85		305	V AC	
Input Voltage Range	DC input		120		430	V DC	
Input Voltage Frequency		'	47		63	Hz	
In most Commont	115V AC				1.2		
Input Current	230V AC			<b>-</b> -	0.8	] , [	
Inrush Current	115V AC	Cold start		30		A	
Initusti Current	230V AC	Cold start		60		]	
Leakage Current	277V AC	'		<0.75m	A		
Hot Plug	Unavailable			ble			





### **Output Specifications**

Item	Operating	g Conditions	Min.	Тур.	Max.	Unit	
O. t t \ / -  t A	Full land name	5V		±2			
Output Voltage Accuracy	Full load range	12V/15V/24V/48V		±1		1	
Line Regulation	Rated load			±0.5		%	
Load Degulation	0%-100% load	5V		±1		<u> </u>	
Load Regulation	0%-100% load	12V/15V/24V/48V		±0.5			
		5V		80			
Dipple & Noice*	20MHz bandwidth	12V/15V	-	120		mV	
Ripple & Noise*	(peak-peak value)	24V		150		] ""	
		48V		240			
Temperature Coefficient				±0.03		%/°C	
Minimum Load			0			%	
Stand-by Power Consumption					0.5	W	
	115V AC		8				
Hold-up Time	230V AC		30		ms		
Short Circuit Protection	Recovery time < 5s disappear.	after the short circuit	Hiccu	Hiccup, continuous, self-recovery			
Over-current Protection	230VAC, Rated	Normal temperature, Hightemperature	110%-200% lo, self-recovery			,	
	load	Low temperature	2	≥110% lo, self-recovery			
	5V	≤6.3VDC (Clamp, self-recovery)					
Over-voltage Protection	12V	≤16.2VDC (Hiccup, self-recovery)					
	15V	≤21.75VDC (Hiccup, self-recovery)					
	24V	≤33.6VDC (Hiccup, self-recovery)					
	48V	≤60VDC (Hiccup, self-recovery)					

Note: \*The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information.

## **General Specifications**

Item		Operating Conditions	Min.	Тур.	Max.	Unit
	Input - 🖶	Electric strength test for 1min., leakage current <10mA		-		
Isolation	Input-output			-		V AC
	Output - 🖶					
	Input - 🖶		100			
Insulation Resistance	Input-output	At 500V DC	100	-		МΩ
rtoolotarioc	Output - 🖶		100			





Item	Operating Conditions				Min.	Тур.	Max.	Unit
Operating Temperature					-30		+70	ာင
Storage Temperature							+85	
Operating Humidity	Non condons	ina			20		90	%RH
Storage Humidity	Non-condens	sirig					95	70KH
Switching Frequency						65		kHz
		85VAC-10	00VAC	-30°C to -25°C	6			
Power Derating	Operating	- 1	85VAC- 165VAC	+40°C to +70°C	2			%/°C
	temperature derating		165VAC- 305VAC	+50°C to +70°C				
		Other output	85VAC- 305VAC	+50°C to +70°C				
	Input volt-	85V AC-100V AC			1.33			%/V AC
	age derat- ing	277V AC - 305V AC			0.72			
Safety Standard							L62368/E 8/GB494	N60335/ 3
Safety Certification					IEC/EN/UL62368/EN60335/ EN61558/ GB4943			
Safety Class						CL	ASS I	
MTBF	MIL-HDBK-2	17F@25°C				>300	),000 h	

Mechanical Specifications				
Case Material	Metal (AL1100, SGCC)			
Dimensions	99mm × 82mm × 30mm			
Weight	190g (Typ.)			
Cooling Method	Free air convection			


## **EMC Specifications**


	CE	CISPR32/EN55032	CLASS B	
Emissions	RE	CISPR32/EN55032	CLASS B	
	Harmonic current	IEC/EN61000-3-2	CLASS A	
	ESD	IEC/EN 61000-4-2	Contact ±6KV/Air ±8KV	perf. Criteria A
	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A
	EFT	IEC/EN 61000-4-4	±2KV	perf. Criteria A
Immunity	Surge	IEC/EN 61000-4-5	line to line ±2KV/line to ground ±4KV	perf. Criteria A
	CS	IEC/EN61000-4-6	10 Vr.m.s	perf. Criteria A
	Voltage dips, short interruptions and voltage variations immunity	IEC/EN61000-4-11	0%, 70%	perf. Criteria B






#### **Product Characteristic Curve**







Note: 1. With an AC input voltage between 85-100VAC and a DC input between 120-140VDC the output power must be derated as per the temperature derating curves;

2. This product is suitable for applications using natural air cooling; for applications in closed environment please consult FAE.





#### **Dimensions and Recommended Layout**







#### Notes:

- 1. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75% RH with nominal input voltage and rated output load;
- 2. The room temperature derating of 5°C/1000m is needed for operating altitude greater than 2000m;
- 3. All index testing methods in this datasheet are based on our company corporate standards;
- 4. In order to improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. The out case needs to be connected to the earth (😩) of system when the terminal equipment in operating;
- 8. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.
- 9. The power supply is considered a component which will be installed into a final equipment. All EMC tests should be confirmed with the final equipment. Please consult our FAE for EMC test operation instructions.

#### **Part Number Table**

Description	Part Number
Enclosed Power Supply, 50W, 5V DC, 10A	MPM50-23B05
Enclosed Power Supply, 50W, 12V DC, 4.2A	MPM50-23B12
Enclosed Power Supply, 50W, 15V DC, 3.4A	MPM50-23B15
Enclosed Power Supply, 50W, 24V DC, 2.2A	MPM50-23B24
Enclosed Power Supply, 50W, 48V DC, 1.1A	MPM50-23B48

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

