

MEDICAL WALL MOUNT INTERCHANGEABLE BLADE POWER SUPPLY 9VDC 5.4 WATT



STONTRONICS: UES06W09060



Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals

Description:

Our range of 5.4 Watt Medical Interchangeable wall plug power supplies provide 5.4 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro, USA & Auz AC Heads , all Efficiency Level VI and carry worldwide safety approvals.

Specification	
Part Code	y - 0 †
Input Voltage Range	90-264 Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.2A at 90VAC
Input AC Heads	UK, Euro, USA & Auz
Output Voltage Rating	+9V
Output Current Range	0.6A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm centre positive – Straight
Total Output Regulation	+/-5
Line and Load Regulation	+/-2
Ripple & Noise	150mVp-p
Efficiency	78.35%Min
Over Voltage Protection	120-150% Rated output voltage input to reset
Over Load Protection	120-150% Rated output power, Auto recovery
Operating Temperature	0°C to +40°C
Storage Temperature	-20°C to +60°C
Operating Humidity	10% to 90%
Storage Humidity	5% to 90%
Hi-Pot	4000VAC 10mA 1min
Leakage Current	<0.1mA max
Safety Standard	Meet ES60601 EN60601 IEC60601 RCM.
EMI Standard	EN55022:2010, CISPR 11:2009/A1:2010
MTBF	50K Hours
Size mm max.	73.5(L) x 42.5(W) x 30.7(H) mm
Weight	85 g

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


STONTRONICS

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

MEDICAL WALL MOUNT INTERCHANGEABLE BLADE POWER SUPPLY 9VDC 5.4 WATT

STONTRONICS: UES06W09060

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.