TE Internal #: 2379907-1

Crimp Terminal Housings, Receptacle, Receptacle, 3 Position, Straight, UL 94V-0, Natural, PBT GF15, Contact Mating Retention,

Mating Alignment, Bag

View on TE.com >



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings











Terminal Type: Receptacle

Housing Type: Receptacle
Number of Positions: 3

Terminal Orientation: Straight
UL Flammability Rating: UL 94V-0

Features

Product Type Features

1 Todaet Type Teatares	
Housing Type	Receptacle
Insulated	No
Configuration Features	
Number of Positions	3
Body Features	
Primary Product Color	Natural
Contact Features	
Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With
Mechanical Attachment	
Mating Alignment	With

PBT GF15

Housing Features

Housing Material



Centerline (Pitch)	8 mm[.315 in]
Usage Conditions	
Operating Temperature Range	-40 - 105 °C[-40 - 120 °F]
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





Documents

Product Drawings

250 HSG REC. F-SPRING 10MM 8MM 3P NAT.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2379907-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2379907-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2379907-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English