

SIGNAL CONDITIONERS AND FLOW SENSORS



FP85A Series

Basic Unit

- ✓ Front Panel Programming and Scaling
- ✓ Alphanumeric Program Display
- ✓ Both Rate and Total Indication Standard
- ✓ NEMA-4X/IP65 Front Face
- ✓ Suitable for Panel Mounting

The FP85A microprocessor-based signal conditioner provides the ultimate in system flexibility and convenience, with simultaneous 4-20 mA and open collector pulse outputs. The FP85A can be integrally mounted to FP8500 series paddlewheel sensors utilizing an FP85NM or FP85DM integral mounting kit. The FP85A can also be remotely mounted, either on a panel (front mounted, utilizing the included captive self-tapping screws to thread into the panel wall) or on a pipe, wall, or tank with a universal mounting kit. The FP85A can be remotely used with the OMEGA® FP-5100, FP-5200, FP-5300, FP-3-1500, and FP-6000 paddlewheel flow sensors.

The three front keys control all programming and scaling of the FP85A – there are no pots to tweak or internal adjustments to make. Simply enter the K-factor, and the FP85A displays rate with field-adjustable decimal point, mA output value, total (field selectable for resettable or non-resettable operation), and the date of the last reprogramming. The 8-digit alphanumeric LCD shows every program step in clear language, allowing display in any engineering units and timebase in seconds, minutes, hours, or days. A special pushbutton sequence permits entry into the programming, thus providing security against unauthorized reprogramming. The FP85A also has a 4.00 mA or a 20.00 mA output calibration signal for scaling remote readout devices.

The front panel of the FP85A is rated NEMA-4X/IP65, and the captive silicone gasket ensures moisture resistance in all mounting configurations.



Shown Smaller Than Actual Size

SPECIFICATIONS

Enclosure: NEMA-4X (IP65) glass-filled polypropylene, with silicone rubber (captive) gasket and 8-32 self-tapping black oxide (captive) screws
Display: 8-digit alphanumeric dot matrix

Display Ranges: Flow, 0.01 to 9999. units; 8-digit total
Display Accuracy: ±0.1% of reading ±0.03% of total reading
Sensor Accuracy: ±0.2 fps
Loop Resolution: ±5 microamps
Loop Accuracy: ±5 mA

To Order (Specify Model No.)

Model No.	Description
Signal Conditioning Module	
FP85A	Programmable module with 4-20 mA and pulse outputs
Sensors for integral mounting (requires FP85NM or FP85DM integral mounting hardware) Accuracy = ±0.1 fps	
FP8501	½" to 4" pipe, polypropylene body/titanium shaft
FP8502	5" to 8" pipe, polypropylene body/titanium shaft
FP8503	½" to 4" pipe, PVDF body/Hastelloy C shaft
FP8504	½" to 4" pipe, all PVDF material

For all-plastic units with PVDF shaft, add suffix **"-AP"** to sensor model number and add to price.

Model No.	Description
Integral mounting kit, for mounting on top of FP85XX sensors	
FP85NM	Integral mounting with ½" NPT conduit ports
FP85DM	Same as FP85NM, with PG13.5 threaded DIN conduit ports
Universal mounting kit, for remote mounting on pipe or wall	
FP85UNM	Universal mounting with ½" NPT conduit ports
	Same as DP85UNM, with PG13.5 threaded DIN conduit ports

Comes with complete operator's manual.


Ordering Example: FP85A, signal conditioning module with 4-20 mA and pulse outputs, plus FP8501A, paddlewheel flow sensor for ½" or 4" pipe with a polypropylene body, plus FP85NM, integral mounting kit with ½" NPT conduit port, . Fitting required; see pages F-63 and F-64.

With Simultaneous Frequency and 4-20 mA Outputs




INSTALLATION STYLES


(PIPE INSTALLATION FITTINGS ARE FOUND ON PAGES F-63 AND F-64)




Panel mount



Pipe mount



Wall mount



Integral

Sensor Wetted Parts:

FP8501A, FP8502A: body: glass-filled polypropylene; shaft: titanium (PVDF optional); rotor: PVDF

FP8503A: body and rotor: PVDF; shaft: Hastelloy C (PVDF optional)

Loop Power:

2-wire mode: 17 to 30 Vdc @ 20 mA max

3-wire mode: 17 to 30 Vdc @ 68 mA max

Current Output: 4 to 20 mA, 2-wire

Loop Impedance: 50 Ω max. @ 10 Vdc; 100 Ω max.

@ 12 Vdc; 1000 Ω max. @ 30 Vdc

Pulse Output: Sensor frequency, optically isolated open-collector transistor, max. current sink 10 mA @ 30 Vdc

Frequency Range: 0.5 to 500 Hz max., scalable from 0.01 to 9999 engineering units

Response Time: Loop: 100 ms; **Display:** 1 sec



Operating Ambient: -15 to 70°C (5 to 158°F)

Storage Temp.: -15 to 80°C (5° to 176°F)



Shipping Wt: 0.5 kg (1 lb) for each item



FP8500 Series Flow Sensor



Dimensions in mm (in)





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters