




## Contour-Ty® Cable Ties – Weather Resistant Nylon 6.6

- Greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers’ arms/hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



Part Number	Length		Width		Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N			
<b>Miniature Cross Section</b>													
CBR1M-M0	4.1	104	0.098	2.5	0.038	1.0	1.00	25	18	80	GTS-E, GS2B-E, PTS, PPTS, STS2	1000	50000
CBR1.5M-M0	5.8	147	0.098	2.5	0.042	1.1	1.50	38					
CBR2M-M0	7.3	185	0.098	2.5	0.042	1.1	2.00	51				18	80
<b>Intermediate Cross Section</b>													
CBR1.5I-M0	5.9	150	0.140	3.6	0.040	1.0	1.50	38	40	178	GTS-E, GS2B-E, PTS, PPTS, STS2	1000	25000
CBR3I-M0	10.4	264	0.140	3.6	0.052	1.3	3.00	76	40	178			
CBR4I-M0	13.6	345	0.140	3.6	0.052	1.3	4.00	102				1000	10000
<b>Standard Cross Section</b>													
CBR2S-M0	7.6	193	0.190	4.8	0.044	1.1	2.00	51	50	222	GTS-E, GS2B-E, GTH-E, GS4H-E, PTS, PTH, PPTS, STS2, STH2	1000	10000
CBR3S-M0	10.8	274	0.190	4.8	0.052	1.3	3.00	76	50	222			
CBR4S-M0	14.0	356	0.190	4.8	0.052	1.3	4.00	102				1000	5000
<b>Heavy-Standard Cross Section</b>													
CBR2HS-D0	8.0	203	0.250	6.4	0.058	1.4	2.00	51	85	378	GTH-E, GS4H-E, GS4EH-E, PTH, STH2, ST3EH	500	5000
<b>Light-Heavy Cross Section</b>													
CBR4LH-TL0	14.6	371	0.300	7.6	0.070	1.8	4.00	102	120	534	GTH-E, GS4H-E, GS4EH-E, PTH, STH2, ST3EH	250	2500
CBR6LH-C0	20.9	531	0.300	7.6	0.070	1.8	6.00	152	120	534		100	2000

B1

B2

B3

C1

C2

C3

C4

D1

D2

D3

E1

E2

E3

E4

E5

F

G

H