

TE Internal #: 2386894-1
 Hand Crimping Tools, Commercial Crimp Tooling, Operator
 Releasable & Adjustable, Removable/Interchangeable, TE Product
 Specification (114-), Manual

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
 Ratchet Configuration: **Operator Releasable & Adjustable**
 Die Sets Type: **Removable/Interchangeable**
 Specification Type: **TE Product Specification (114-)**
 TE Certification: **Cannot be Certified**

Features

Other

| | |
|-----------------------|----------------------------------|
| Tool Grade | Commercial Crimp Tooling |
| Ratchet Configuration | Operator Releasable & Adjustable |
| Die Sets Type | Removable/Interchangeable |
| Specification Type | TE Product Specification (114-) |
| TE Certification | Cannot be Certified |
| Power Technology Type | Manual |
| Tooling Type | SDE Crimp Hand Tool |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (.11% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |





| | |
|---------------------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|---|--|--|--|
|  <p>TE Part # 2386894-2 SDE F SYSTEM CONTACT 1.50-2.50 DIE SET</p> |  <p>TE Part # 2362810-1 SDE CRIMP HAND TOOL FRAME W /O DIES</p> | <p>TE Part # 927789-4 SOCKET CONTACT 2,5MM DIA (LOOSE PIECE)</p> | <p>TE Part # 927788-3 SOCKET CONTACT 2,5MM DIA</p> |
| <p>TE Part # 927789-3 KONTAKT BU 2,5MM D</p> | <p>TE Part # 927801-4</p> | <p>TE Part # 927800-2</p> | <p>TE Part # 927788-2</p> |
| <p>TE Part # 927788-4</p> | <p>TE Part # 927788-5</p> | <p>TE Part # 927800-4</p> | <p>TE Part # 927800-5</p> |

Documents



Datasheets & Catalog Pages

Bottoming Dies

English

INSTALITE Molded Boots with Rayaten

English

Instruction Sheets

Instruction Sheet (U.S.)

English