enetSEAL+

TE Internal #: 2325102-1

PCB Mount Header, Vertical, Wire-to-Board, 2 Position, 2.54 mm [.1 in] Centerline, Fully Shrouded, Unplated, Through Hole - Solder,

Sealable, Signal

View on TE.com >



Connectors > PCB Connectors > PCB Headers & Receptacles











Connector System: Wire-to-Board

Number of Positions: 2

Centerline (Pitch): 2.54 mm [.1 in]

Sealable: Yes

PCB Mount Orientation: Vertical

Features

Product Type Features

Troduct Type reducted	
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
Number of Sections	1
Number of Positions	2
PCB Mount Orientation	Vertical
Number of Rows	1
Electrical Characteristics	
Operating Voltage	33 VAC



Primary Product Color	Black
Connector Code	A
Contact Features	
Contact Size	8mm
Contact Type	Tab
Mating Tab Width	1.2 mm[.047 in]
Mating Tab Thickness	.6 mm[.024 in]
Contact Mating Area Plating Material	Unplated
Contact Current Rating (Max)	10 A
Termination Features	
Termination Method to Printed Circuit Board	Through Hole - Solder
	Through Hole - Solder
Termination Method to Printed Circuit Board	Through Hole - Solder With
Termination Method to Printed Circuit Board Mechanical Attachment	
Termination Method to Printed Circuit Board Mechanical Attachment Mating Alignment	With
Termination Method to Printed Circuit Board Mechanical Attachment Mating Alignment Connector Mounting Type	With
Termination Method to Printed Circuit Board Mechanical Attachment Mating Alignment Connector Mounting Type Housing Features	With Board Mount
Termination Method to Printed Circuit Board Mechanical Attachment Mating Alignment Connector Mounting Type Housing Features Centerline (Pitch)	With Board Mount
Termination Method to Printed Circuit Board Mechanical Attachment Mating Alignment Connector Mounting Type Housing Features Centerline (Pitch) Usage Conditions	With Board Mount 2.54 mm[.1 in]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-onreach

Compatible Parts



2POS,MCON 1.2,REC HSG ASSY,SLD, COD A



MNTG CLIP, ENETSEAL PLUS











Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2325102-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2325102-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2325102-1_A.3d_stp.zip

PCB Mount Header, Vertical, Wire-to-Board, 2 Position, 2.54 mm [.1 in] Centerline, Fully Shrouded, Unplated, Through Hole - Solder, Sealable, Signal



English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English