

Note: This datasheet may be out of date. Please download the latest datasheet of GCM1885C2A1R0BA16# from the official website of Murata Manufacturing Co., Ltd.

"#" indicates a package specification code.

http://www.murata.com/en/products/productdetail?partno=GCM1885C2A1R0BA16%23

GCM1885C2A1R0BA16#

In Production















< List of part numbers with package codes > GCM1885C2A1R0BA16D GCM1885C2A1R0BA16J



Appearance & Shape







References

| Packaging | Specifications | Standard |
|-----------|------------------|----------|
| | | Packing |
| | | Quantity |
| D | 180mm Paper Tape | 4000 |
| J | 330mm Paper Tape | 10000 |

| Mass (typ.) | | |
|-------------|-------|--|
| 1 piece | 6.3mg | |
| φ180mm Reel | 144g | |

1 of 4

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





GCM1885C2A1R0BA16#

Note: This datasheet may be out of date.

Please download the latest datasheet of GCM1885C2A1R0BA16# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GCM1885C2A1R0BA16%23

"#" indicates a package specification code.



Specifications

| Length | 1.6±0.1mm |
|--|----------------|
| Width | 0.8±0.1mm |
| Thickness | 0.8±0.1mm |
| Capacitance | 1.0pF ±0.1pF |
| Distance between external terminals g | 0.5mm min. |
| External terminal size e | 0.2 to 0.5mm |
| Operating Temperature Range | -55°C to 125°C |
| Rated Voltage | 100Vdc |
| Size code in inch(mm) | 0603 (1608M) |
| тс | 0±30ppm/°C |
| Temperature characteristics (complied standard) | C0G(EIA) |
| Temperature range of temperature characteristics | 25°C to 125°C |

2 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date. Please download the latest datasheet of GCM1885C2A1R0BA16# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GCM1885C2A1R0BA16%23


"#" indicates a package specification code.


GCM1885C2A1R0BA16#





Characteristic Data

The charts below may show another part number which shares its characteristics.









GCM1885C2A1ROBA16 C-AC Voltage capchange, DCOV, 25.0d

3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Product Search Data Sheet


Note: This datasheet may be out of date.

Please download the latest datasheet of GCM1885C2A1R0BA16# from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en/products/productdetail?partno=GCM1885C2A1R0BA16%23

"#" indicates a package specification code.

GCM1885C2A1R0BA16#



GCM1885C2A1R0BA16 C-Temp. capchange, DCOV, AC1Vrms



GCM1885C2A1R0BA16 S21 DCOV, 25degC

4 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

