




## RX 8144

### ERGO™ Flush Precision Cut Diagonal Cutter with Tapered Head 0.1-1.25 mm











#### PRODUCT DETAILS

- Precision Tapered Head diagonal cutters developed according to the scientific ERGO™ process, Tapered Head
- ERGO™ handles with two-component combination and thermoplastic surface for comfortable grip, on tough polypropylene core for rigidity
- Micro-bevel, flush & ultra-flush cut
- The stated cutting capacity is for copper wire
- Cutting capacity: 0.1-0.8 mm to 0.2-1.25 mm
- High performance alloy steel
- Burnished finish
- Numerically controlled machine grinding ensures edge angle accuracy and contact, increasing tool reliability and consistency
- Precision induction-hardened edges 63-65 HRC
- Screw joint minimises friction and maximises alignment of cutting edges
- ESD safe handles in two-component synthetic material
- Bio spring limits tension through the working cycle of the tool and can be adjusted to 3 different positions or removed
- Ideal for assembly work where accessibility is a consideration



PRODUCT ATTRIBUTES

Product: **RX 8144**

	Tapered		S		Flush
	0.1-1.25 mm		0.00-0.05 in		
		<b>A</b>	135.5 mm	<b>A</b>	5.25 in
<b>B</b>	10,5 mm	<b>B</b>	0,41 in	<b>C</b>	8 mm
<b>C</b>	0.39 in	<b>D</b>	6 mm	<b>D</b>	0,24 inch
<b>F</b>	0,8 mm	<b>F</b>	0,03 in		68 g
<b>Ω</b>	Dissipative				