

GRM42A7U3F330JW31#

“#” indicates a package specification code.



< List of part numbers with package codes >
GRM42A7U3F330JW31L

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
L	180 Embossed Tape	3000

Mass (typ.)	
1 piece	54.0mg

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM42A7U3F330JW31#

“#” indicates a package specification code.



Specifications

Length	4.5±0.3mm
Width	2.0±0.2mm
Thickness	1.0+0/-0.3mm
Capacitance	33pF ±5%
Distance between external terminals g	2.9mm min.
External terminal size e	0.3mm min.
Operating Temperature Range	-55°C to 125°C
Rated Voltage	3150Vdc
Size code in inch(mm)	1808 (4520M)
TC	-750±120ppm/°C
Temperature characteristics (complied standard)	U2J(EIA)
Temperature range of temperature characteristics	25°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


GRM42A7U3F330JW31#

"#" indicates a package specification code.




Characteristic Data


The charts below may show another part number which shares its characteristics.




■ GRM42A7U3F330JW31 |Z| DC0V, 25degC



■ GRM42A7U3F330JW31 R DC0V, 25degC



■ GRM42A7U3F330JW31 C-DC bias capchange, 25.0degC, AC1V



■ GRM42A7U3F330JW31 C-AC Voltage capchange, DC0V, 25.0d


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM42A7U3F330JW31#


“#” indicates a package specification code.

Temperature Characteristics



■ GRM42A7U3F330JW31 C-Temp. capchange, DCOV, AC1Vrms

S Parameter S21



■ GRM42A7U3F330JW31 S21 DCOV, 25degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.