Micro Relay A TE Internal #: 4-1904124-2 Micro Relay A, Micro Relays, 12VDC Rated Coil Voltage, Micro Relay Contact Current Class 20 – 30 A, Micro Relay Contact Arrangement 1 Form A (NO)

View on TE.com >



Relays, Contactors & Switches > Relays > Automotive Relays > Automotive Plug-In Relays > Micro Relays



Rated Coil Voltage:12 VDCMicro Relay Contact Current Class:20 – 30 AMicro Relay Contact Arrangement:1 Form A (NO)Micro Relay Coil Resistance:119 ΩMounting Brackets:Without

Features

Product Type Features

Relay Type

Micro Relay A/VFMA

Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	500 Vrms
Current Rating (85°C)	30 A
Coil Power Rating Class	>1.5W
Contact Limiting Short-Time Current	150 A
Insulation Initial Dielectric Between Contacts and Coil	500 Vrms
Insulation Initial Dielectric Between Coil/Contact Class	0 – 500 V
Coil Power Rating (DC)	1600 mW
Contact Limiting Making Current	120 A
Contact Limiting Continuous Current	30 A
Coil Magnetic System	Monostable, DC
Rated Voltage	12 VDC
Contact Limiting Breaking Current	30 A
Contact Switching Load (Min)	1000mA @ 5VDC
Rated Coil Voltage	12 VDC
Micro Relay Coil Resistance	119 Ω

4-1904124-2

Micro Relay A, Micro Relays, 12VDC Rated Coil Voltage, Micro Relay Contact Current Class 20 – 30 A, Micro Relay Contact Arrangement 1 Form A (NO)



Body Features	
Weight	16 g[.565 oz]
Contact Features	
Terminal Type	Plug-In, Quick Connect
Contact Base Material	Ag Alloy
Micro Relay Contact Current Class	20 – 30 A
Micro Relay Contact Arrangement	1 Form A (NO)
Mechanical Attachment	
Mounting Type	Plug-In
Dimensions	
Width Class (Mechanical)	12 – 16 mm
Height	25.4 mm[1 in]
Length Class (Mechanical)	20 – 25 mm
Height Class (Mechanical)	25 – 30 mm
Width	15.5 mm[.61 in]
Length	23 mm[.906 in]

Usage Conditions

Environmental Ambient Temperature Class	105 – 125°C
Environmental Ambient Temperature (Max)	125 °C[257 °F]
Other	
Mounting Brackets	Without
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

4-1904124-2

Micro Relay A, Micro Relays, 12VDC Rated Coil Voltage, Micro Relay Contact Current Class 20 – 30 A, Micro Relay Contact Arrangement 1 Form A (NO)



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Also in the Series | Micro Relay A




Customers Also Bought



4-1904124-2

Micro Relay A, Micro Relays, 12VDC Rated Coil Voltage, Micro Relay Contact Current Class 20 – 30 A, Micro Relay Contact Arrangement 1 Form A (NO)





Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1904124-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1904124-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1904124-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages Automotive Relay Application Notes

English

Micro Relay A, Micro ISO, Plug-in

English

Product Specifications Definitions, Handling, Processing, Testing and Use of Relays

English