

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200688193](#)  
**Status:** **Active**  
**Overview:** Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable  
**Description:** Micro-Change (M12) In-Line Splitter with Knurled Hexnuts, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), WSOR Cable, 0.60m (1.97') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E152210

**General**

Product Family Industrial Tees and Splitters  
 Series [120009](#)  
 IP Rating IP67  
 Overview [Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable](#)  
 Product Name Micro-Change (M12)  
 Taxonomy Industrial Tees and Splitters  
 Type Splitter - In-line  
 UPC 889056131087

**Physical**

Color - Cable Jacket Black  
 Drop Connector N/A  
 Drop Gender N/A  
 Keyway Single  
 LED Indicator No  
 Left Trunk Connector Micro-Change (M12)  
 Left Trunk Gender Male  
 Leg 1 Length 0.60m  
 Leg 2 Length 0.60m  
 Material - Cable Jacket TPU  
 Material - Connector Body TPU  
 Material - Coupling Nut Nickel-plated Brass  
 Net Weight 81.484/g  
 Poles 3 Female/4 Male  
 Right Trunk Connector Micro-Change (M12)  
 Right Trunk Gender Female  
 Temperature Range - Operating -25°C to +80°C

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 60V

**Material Info**

Engineering Number 884A30B30M006

**Reference - Drawing Numbers**

Sales Drawing SD-120068-002-001, SD-120068-002-002



*Series image - Reference only*

**EU ELV**

**Compliant with Exemption 3**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)  
 Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Compliant with

Exemption 3

Not Contained

CER\_4000408954\_00\_000.pdf

CER\_4000410542\_00\_000.pdf

**Search Parts in this Series**

120009 Series