



DDR4 DIMM

TE Internal #: 2199155-1

DDR4 DIMM, DIMM Sockets, Double Data Rate (DDR) 4, Board-to-Bus Bar, 288 Position, Surface Mount, Vertical Module Orientation

[View on TE.com >](#)

Connectors > Socket Connectors > Memory Sockets > DIMM Sockets > DDR4 DIMM SOCKETS



DRAM Type: **Double Data Rate (DDR) 4**

Connector System: **Board-to-Bus Bar**

Number of Positions: **288**

PCB Mounting Style: **Surface Mount**

Module Orientation: **Vertical**

[All DDR4 DIMM SOCKETS \(69\)](#)

Features

Product Type Features

DRAM Type	Double Data Rate (DDR) 4
Connector System	Board-to-Bus Bar
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	288
Module Orientation	Vertical

Body Features

Ejector Type	Standard
--------------	----------

Contact Features

Contact Current Rating (Max)	.75 A
------------------------------	-------

Mechanical Attachment

PCB Mounting Style	Surface Mount
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	.85 mm[.033 in]
--------------------	-----------------



Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Hard Tray
------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2822979-3
LGA3647-0 SOCKET P0 KIT FOR ODM (30U AU)

TE Part # 2199155-5
DDR4 DIMM 288 PIN SMT TYPE

TE Part # 2199155-7
DDR4 DIMM 288 Pin SMT type

TE Part # 5-2199155-5
DDR4 DIMM 288 Pin SMT type

TE Part # 5-2199155-6
DDR4 DIMM 288 Pin SMT type

TE Part # 5-2368060-7
DDR4 DIMM 288 Pin SMT type

TE Part # 5-2368060-8
DDR4 DIMM 288 Pin SMT type

Also in the Series | DDR4 DIMM

DIMM Sockets(69)

SO DIMM Sockets(39)

Customers Also Bought

TE Part #1879378-9
TLR 2512 2.0W R001 1% 50PPM 2K RL

TE Part #1-406541-6
MJ,INV,1X1,6PNL G,.140"ST,SN

TE Part #1551920-2
zQSFP+ connector assembly

TE Part #1551891-1
Cage Assy, Behind Bezel, QSFP28

TE Part #1551920-1
zQSFP+ connector assembly


TE Part #1879233-6
SMW5 R16 5%

TE Part #1734774-7
PCI EXP 3.1L 64 POS BLK G/F

TE Part #1410278-2
MULTIGIG RT PWR .8" VRT RCP 2P PBFR



TE Part #1775838-2
mSATA/mini PCI-E 5.6H Type I G/F



TE Part #7-1437532-6
540-AG10D=SOCKET ASSY

Documents

Product Drawings

[DDR4 DIMM 288 Pin SMT type](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_2199155-1_B.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2199155-1_B.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2199155-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DDR4 DIMM Socket Flyer \(English\)](#)

English

[DDR4 DIMM Socket Flyer \(Chinese\)](#)

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[MD_2199155-1_0922201713_dmtec](#)

English

[MD_2199155-1_0922201713_dmtec](#)

English