



HX-CT

TE Internal #: EL8200-000

HX-CT, Printable Tubing, Continuous Printable Tubing Type, Low Fire Hazard Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio, White

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE LOW FIRE HAZARD HX-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Low Fire Hazard**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **White**

Supplied Inner Diameter: **19 mm [ .75 in ]**

[All CONTINUOUS TUBE LOW FIRE HAZARD HX-CT \(18\)](#)

**Features**

**Product Type Features**

|                        |                 |
|------------------------|-----------------|
| Printable Tubing Type  | Continuous      |
| Printable Tubing Grade | Low Fire Hazard |

**Body Features**

|                               |       |
|-------------------------------|-------|
| Printable Tubing Shrink Ratio | 2:1   |
| Primary Product Color         | White |

**Dimensions**

|                                 |                              |
|---------------------------------|------------------------------|
| Supplied Inner Diameter         | 19 mm[.75 in]                |
| Recovered Inside Diameter       | 9.5 mm[.374 in]              |
| Compatible Cable Diameter Range | 9.5 – 15.28 mm[.375 – .6 in] |

**Usage Conditions**

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

**Operation/Application**

|                    |  |
|--------------------|--|
| Recommended Ribbon | See TE Document 411-121005 the Printer Product Ribbon Matrix |
|--------------------|--|

**Printer/Label Features**

|                     |  |
|---------------------|--|
| Recommended Printer | See TE Document 411-121005 the Printer |
|---------------------|--|



|                    |                       |
|--------------------|-----------------------|
|                    | Product Ribbon Matrix |
| Printer Technology | Thermal Transfer      |

### Packaging Features

|                    |    |
|--------------------|----|
| Packaging Quantity | 50 |
|--------------------|----|

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUL 2021 (219)<br>Candidate List Declared Against: JAN 2021 (211)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not applicable for solder process capability  |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




### Compatible Parts



### Also in the Series | HX-CT



### Customers Also Bought





## Documents

### Product Drawings

[HX-CT-50M-19.0-OUT-9](#)

English

---

### Datasheets & Catalog Pages

[HX-CT, Low Fire Hazard Continuous Heat Shrink Identification Tube](#)

English

---

### Product Specifications

[HX - LFH Heat Shrink Sleeving](#)

English

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English