



HT-CT

TE Internal #: EL8071-000

HT-CT, Printable Tubing, Continuous Printable Tubing Type, High Temperature Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio, Yellow

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE HIGH TEMPERATURE HT-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **High Temperature**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **Yellow**

Supplied Inner Diameter: **3.2 mm [.125 in]**

[All CONTINUOUS TUBE HIGH TEMPERATURE HT-CT \(14\)](#)

Features

Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	High Temperature

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	Yellow

Dimensions

Supplied Inner Diameter	3.2 mm[.125 in]
Recovered Inside Diameter	1.57 mm[.062 in]
Compatible Cable Diameter Range	1.75 – 2.66 mm[.069 – .105 in]

Usage Conditions

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer
---------------------	--



Product Ribbon Matrix

Printer Technology Thermal Transfer

Packaging Features

Packaging Quantity 50

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JUL 2021 (219)
 Candidate List Declared Against: JAN 2021 (211)
 SVHC > Threshold:
 Not Yet Reviewed

Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts








Also in the Series | HT-CT



Customers Also Bought



Documents

Product Drawings

[HT-CT-50M-1/8-OUT-4](#)

English

Datasheets & Catalog Pages

[HT-CT, Continuous High Temperature Heat Shrink Identification Tube](#)

English



Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English