



HX-CT

TE Internal #: EL8206-000

HX-CT, Printable Tubing, Continuous Printable Tubing Type, Low Fire Hazard Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio, Yellow

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > CONTINUOUS TUBE LOW FIRE HAZARD HX-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Low Fire Hazard**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **Yellow**

Supplied Inner Diameter: **6.4 mm [ .25 in ]**

[All CONTINUOUS TUBE LOW FIRE HAZARD HX-CT \(18\)](#)

**Features**

**Product Type Features**

Printable Tubing Type	Continuous
Printable Tubing Grade	Low Fire Hazard

**Body Features**

Printable Tubing Shrink Ratio	2:1
Primary Product Color	Yellow

**Dimensions**

Supplied Inner Diameter	6.4 mm[.25 in]
Recovered Inside Diameter	3.2 mm[.125 in]
Compatible Cable Diameter Range	3.2 – 5.12 mm[.125 – .201 in]

**Usage Conditions**

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

**Operation/Application**

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

**Printer/Label Features**

Recommended Printer	See TE Document 411-121005 the Printer
---------------------	--



	Product Ribbon Matrix
Printer Technology	Thermal Transfer

### Packaging Features

Packaging Quantity	50
--------------------	----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # CP8122-000  
T6112DS-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

### Also in the Series | HX-CT



Printable Tubing(18)

### Customers Also Bought



TE Part #788085-1  
TYPE III+ PIN ASSEMBLY,.062



TE Part #1-2273111-4  
M8 strgt socket to M12 strgt plug AA



TE Part #2-2205132-3  
CA MINI IO MINI IO TYPE II



TE Part #1-2176155-3  
TLM 0805 0.25W R10 5% 100PPM 5K RL



TE Part #EL8205-000  
HX-CT-50M-4.8-OUT-4



TE Part #1633966-2  
CRIMPER, INSULO



TE Part #3-1633738-2  
CRIMPER, WIRE F.040



TE Part #7-2151032-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-205D



## Documents

### Product Drawings

[HX-CT-50M-6.4-OUT-4](#)

English

---

### Datasheets & Catalog Pages

[HX-CT, Low Fire Hazard Continuous Heat Shrink Identification Tube](#)

English

---

### Product Specifications

[HX - LFH Heat Shrink Sleeving](#)

English

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English