

2273115-4 ✓ ACTIVE

TE Internal #: 2273115-4

M8/M12 Cable Assemblies, Sensor/Actuator, 8 Positions, A M8
/M12 Cable Assembly Keying, Plug/Receptacle, M12 to M12,
Straight-Straight

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 MS-FS DOUBLE END CABLE ASSY BL



M8/M12 Application Type: **Sensor/Actuator**

Number of M8/M12 Cable Assembly Positions: **8**

M8/M12 Cable Assembly Keying: **A**

M8/M12 Cable Assembly Connector Type: **Plug/Receptacle**

M8/M12 Cable Assembly Type: **M12 to M12**

[All M12 MS-FS DOUBLE END CABLE ASSY BL \(35\)](#)

Features

Product Type Features

Product Type	Cable Assembly
Cable Type	PUR
M8/M12 Cable Assembly Connector Type	Plug/Receptacle
M8/M12 Cable Assembly Type	M12 to M12
M8/M12 Cable Assembly Shielded	No

Configuration Features

Number of M8/M12 Cable Assembly Positions	8
M8/M12 Cable Assembly Keying	A
M8/M12 Cable Assembly Configuration	Double Ended

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Body Features

Connector Color	Blue
Wire Color	Brown, White, Blue, Black, Gray, Pink, Violet, Orange
Insulation Material	PUR
Cable Jacket Color	Gray



Contact Features

Contact Current Rating	2 A
------------------------	-----

Mechanical Attachment

Screw & Hole Thread Size	M12 x M12
M8/M12 Cable Assembly Mounting Angle	Straight-Straight

Housing Features

M8/M12 Cable Assembly Housing Material	Plastic
--	---------

Dimensions

Overall Outside Cable Diameter	6 mm [.236 in]
Wire Size	.205 mm ²
Cable Assembly Length	1500 mm

Usage Conditions

Operating Temperature Range	-40 – 80 °C [-40 – 176 °F]
-----------------------------	----------------------------

Operation/Application

M8/M12 Application Type	Sensor/Actuator
-------------------------	-----------------

Packaging Features

Packaging Method	Box
Packaging Quantity	1/Carton

Other

Field Serviceable	Yes
-------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





Documents

Product Drawings

[M12 strgt plug to M12 strgt socket AA](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_2273115-4_A.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2273115-4_A.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2273115-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

Product Specifications

[Application Specification](#)

English