

Coaxial Panel Connector 23_716-50-0-57/003_-

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

Mechanical Data

Number of matings	500
Weight	0.0798 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00010926
Catalogue drawing	DCA-00010928

Ordering Information

Bulk 20 pcs package	23_716-50-0-57/003_-V
---------------------	-----------------------