

Stripping and cutting tool

Mini-duro-stripax



Blade set


Stripping and cutting tool for conductors with special insulation types for conductor diameters 0.2 ... 1.21 mm (~ AWG 32 ... 18)

- Flexible and solid conductors with PVC, Teflon (PTFE) and silicone insulation
- Special punch blades do not damage the conductor
- No splicing of the single conductors
- Blade inserts can be easily replaced
- All inserts fit one housing

Technical data

Max. stripping length	mm	3 – 7
Stripping diameter max. cutting performance	mm	2,2
Tool data		
Length	mm	135
Weight	g	110

Selection of blade sets


Conductor diameter

Colour	white	yellow	red	green	blue	black
mm (min./max.)	0.3 – 1.3	0.2 – 0.3	0.3 – 0.5	0.55 – 0.8	0.88 – 0.92	1.0 – 1.21
AWG	28 ... 18	32/1, 32/7, 30/1, 30/7	28/1, 28/7, 28/19, 26/1, 26/7, 26/19, 24/1	24/7, 24/19, 22/1, 22/7, 22/19, 20/1	20/7, 20/19	18/1, 18/7, 18/19
mm ²	≈ 0.08 ... 1.0					
Insulation material	PVC / silicone	PTFE	PTFE	PTFE	PTFE	PTFE

Order data

Tools with blade set (Qty = 1)	Order No. 9001280000	Order No. 9003700000	Order No. 9003710000	Order No. 9003720000	Order No. 9003730000	Order No. 9003740000
Tool with all blade sets (Qty = 1)	Order No. 9003500000					

Accessories

Blade set (Qty = 1)	Order No. 9006970000	Order No. 9003600000	Order No. 9003610000	Order No. 9003620000	Order No. 9003630000	Order No. 9003640000
Set of stripping blades (Mini Stripax up to April 2003)	Order No. 9001290000					