

1-480698-0 ✓ ACTIVE

MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 1-480698-0

Rectangular Power Connectors, Housing, Plug, Wire-to-Board /
Wire-to-Wire, 2 Position, 6.35 mm [.25 in] Centerline, Wire & Cable,
Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Multiple Contact Types	Without
------------------------	---------



Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	6.35 mm [.25 in]
Housing Color	Natural
Housing Material	Nylon

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	Certified, LR 16455
UL Rating	Recognized
Agency/Standard	CSA, UL, VDE
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 640309-6
UMNL PIN 12-10 AU/PHBZ



TE Part # 350551-6
UMNL SOK 20-14 AU/PHBZ L/P



TE Part # 350690-2
UMNL PIN 24-18 AUBR L/P



TE Part # 926902-3
UNIV-MNL SPLIT ST



TE Part # 350550-7
UMNL SOK 20-14 AU/BR L/P



TE Part # 350690-3
UMNL PIN 24-18 PTPPHBZ L/P















TE Part # 350689-7
UMNL SOK 24-18 AUBR L/P












TE Part # 350547-7
UMNL PIN 20-14 AUBR L/P



 <p>TE Part # 350689-2 UMNL SOK 24-18 AUBR L/P</p>	 <p>TE Part # 640310-3 UMNL SOK 12-10 PTPPHBZ</p>	 <p>TE Part # 350689-3 UMNL SOK 24-18 PTPPHBZ L/P</p>	 <p>TE Part # 350690-7 UMNL PIN 24-18 AUBR L/P</p>
 <p>TE Part # 350689-1 UMNL SOK 24-18 PTPBR L/P</p>	 <p>TE Part # 926893-3 UNIV.M-N-L.SOCKET</p>	 <p>TE Part # 350550-6 UMNL SOK 20-14 AU/PHBZ L/P</p>	 <p>TE Part # 350547-3 UMNL PIN 20-14 PTPPHBZ L/P</p>
 <p>TE Part # 350547-2 UMNL PIN 20-14 AUBR L/P</p>	 <p>TE Part # 640713-1 02P UMNL STR/REL & INSERT</p>	 <p>TE Part # 350550-2 UMNL SOK 20-14 AU/BR L/P</p>	 <p>TE Part # 350428-4 02P UMNL PIN HDR ASSY NATL AU</p>

Also in the Series | **Universal MATE-N-LOK**

 <p>Circular Power Connectors(2)</p>	 <p>Connector Contacts(10)</p>	 <p>Insertion & Extraction Tools(4)</p>	 <p>Power Contacts(207)</p>
 <p>Rectangular Boots & Strain Relief(35)</p>	 <p>Rectangular Connector Adapters(7)</p>	 <p>Rectangular Connector Hardware(1)</p>	 <p>Rectangular Connector Housings(1)</p>



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(728)

Customers Also Bought



TE Part #350547-1
UMNL PIN 20-14 PTPBR L/P



TE Part #1-480710-0
15P UMNL PLUG HSG NATL



TE Part #1-480703-0
04P UMNL CAP HSG NATL



TE Part #1-480706-0
09P UMNL PLUG HSG NATL



TE Part #1-480707-0
09P UMNL CAP HSG NATL



TE Part #1-480708-0
12P UMNL PLUG HSG NATL



TE Part #1-480705-0
06P UMNL CAP HSG NATL



TE Part #1-480704-0
06P UMNL PLUG HSG NATL



TE Part #1-480709-0
12P UMNL CAP HSG NATL



TE Part #1-480701-0
03P UMNL CAP HSG NATL

Documents

Product Drawings

[02P UMNL PLUG HSG NATL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-480698-0_BJ.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1-480698-0_BJ.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-480698-0_BJ.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_1-480698-0_0104201967_dmtec](#)

English

[MD_1-480698-0_0104201967_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English