

1-2267796-5 ✓ ACTIVE




TE Internal #: 1-2267796-5

Pluggable I/O Cable Assemblies, Pluggable / Direct Attach,
24AWG Wire Size, .25mm² Wire Size, Cable Assembly Length .984
ft [.3 m], Black, Plug, Plug

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Pluggable I/O Cable Assembly Type: **Pluggable / Direct Attach**

Wire Size: **.25 mm²**

Pluggable I/O Cable Assembly Shielded: **No**

Cable Assembly Length: **.3 m [.984 ft]**

Features

Product Type Features

Latching Style	Pull Tab Release
Product Type	Cable Assembly
Product Designation	Patch Cord
Cable Assembly Category	Industry Standard
Pluggable I/O Cable Assembly Type	Pluggable / Direct Attach
Pluggable I/O Cable Assembly Shielded	No
Pluggable I/O Cable Assembly Connector Type (End A)	Plug
Pluggable I/O Cable Assembly Connector Type (End B)	Plug
Pluggable I/O Cable Assembly Cable Style	Discrete Pairs

Configuration Features

Configuration	Double-Ended
Number of Power Positions	0
Pluggable I/O Cable Assembly Keyed	No

Body Features

Pluggable I/O Cable Assembly Color	Black
------------------------------------	-------



Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Mechanical Attachment

Jackscrew	Without
-----------	---------

Housing Features

Housing Material	Thermoplastic
------------------	---------------

Dimensions

Wire Size	.25 mm ²
-----------	---------------------

Operation/Application

Halogen Free	No
--------------	----

Other

Cable Assembly Length	.3 m [.984 ft]
-----------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Documents

Product Drawings

[CA, MTE MOW-MOW, 6POS, 300mm 15Au, 24AWG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-2267796-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2267796-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2267796-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Datasheet - Ampmodu Mte Off-The Shelf Cable Assemblies](#)

English

[Circular Plastic Connectors Standard Cable Assemblies](#)

English

Product Specifications

[Application Specification](#)

English