

# LM3S6911 Microcontroller



## Product Features

### 32-Bit RISC Performance

- 50-MHz operation with 32-bit ARM® Cortex™-M3 architecture
- Thumb®-compatible Thumb-2-only instruction set, with hardware-division and single-cycle-multiplication
- Integrated Nested Vectored Interrupt Controller (NVIC) provides deterministic interrupt handling
- 30 interrupt channels with eight priority levels
- Memory protection unit (MPU)
- Unaligned data access enables data to be efficiently packed into memory
- Atomic bit manipulation (bit-banding) delivers maximum memory utilization and streamlined peripheral control

### On-Chip Memory

- 256 KB single-cycle flash with two forms of flash protection on a 2-KB block basis
- 64 KB single-cycle SRAM

### Flexible Timer Capability

- Four general-purpose timers, each configurable as one 32-bit or two 16-bit timers
- Real-Time Clock (RTC) capability
- 24-bit system (SysTick) timer
- 32-bit watchdog timer

### 10/100 Ethernet Controller

- Conforms to the IEEE 802.3-2002 Specification
- IEEE 1588-2002 Precision Time Protocol (PTP) compliant
- Full- and half-duplex for both 100 Mbps and 10 Mbps operation
- Integrated 10/100 Mbps Transceiver (PHY)
- Automatic MDI/MDI-X cross-over correction
- Programmable MAC address

### Serial Interfaces

- Two synchronous serial interfaces (SSI) with master and slave modes for SPI, MICROWIRE, or TI synchronous serial
- Two I<sup>2</sup>C interfaces (master and slave)
- Three fully programmable 16C550-type UARTs with IrDA support

### UART

- Three fully programmable 16C550-type UARTs with IrDA support
- Separate 16x8 transmit (TX) and 16x12 receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable baud-rate generator with fractional divider

### Analog Comparators

- Two independent integrated analog comparators
- Configurable for output to: drive an output pin or generate an interrupt
- Compare external pin input to external pin input or to internal programmable voltage reference

### Inter-Integrated Circuit (I<sup>2</sup>C) Interface

- Two I<sup>2</sup>C modules
- Master and slave receive and transmit operation with transmission speed up to 100 Kbps in Standard mode and 400 Kbps in Fast mode
- Interrupt generation
- Master with arbitration and clock synchronization, multimaster support, and 7-bit addressing mode

### GPIOs

- 10-46 GPIOs, depending on configuration
- 5-V-tolerant input/outputs
- Programmable interrupt generation
- Fast toggle capable of a change every two clock cycles

### Power

- On-chip Low Drop-Out (LDO) voltage regulator, with programmable output user-adjustable from 2.25 V to 2.75 V
- Battery-backed hibernation module with real-time clock and 256-bytes of non-volatile memory
- 3.3-V supply brown-out detection
- Low-power options on controller: Sleep and Deep-sleep modes
- Low-power options for peripherals: software controls shutdown of individual peripherals
- User-enabled LDO unregulated voltage detection and automatic reset

### Flexible Reset Sources

- Power-on reset (POR)
- Reset pin assertion
- Brown-out (BOR) detector alerts to system power drops
- Software reset
- Watchdog timer reset
- Internal low drop-out (LDO) regulator output goes unregulated

### Additional Features

- Programmable clock source control
- Clock gating to individual peripherals for power savings
- IEEE 1149.1-1990 compliant Test Access Port (TAP) controller
- Debug access via JTAG and Serial Wire interfaces
- Full JTAG boundary scan

### Package and Temperature

- 100-pin RoHS-compliant LQFP package
  - Industrial-range (-40°C to +85°C)
  - Extended-range (-40°C to +105°C)
- 108-ball RoHS-compliant BGA package
  - Industrial-range (-40°C to +85°C)

## Target Applications

- Motion control
- Factory automation
- Fire and security
- HVAC and building control

# LM3S6911 Microcontroller



LUMINARY MICRO®

- Power and energy
- Test and measurement equipment
- Medical instrumentation

## Ordering Information

Orderable Part Number	Description
LM3S6911-IQC50	Stellaris® LM3S6911 Microcontroller Industrial Temperature
LM3S6911-IQC50 (T) <sup>a</sup>	
LM3S6911-EQC50	Stellaris® LM3S6911 Microcontroller Extended Temperature
LM3S6911-EQC50 (T)	
LM3S6911-IBZ50	Stellaris® LM3S6911 Microcontroller Industrial Temperature
LM3S6911-IBZ50 (T)	

a. T= Tape and Reel.

## Evaluation Kit

The Luminary Micro Stellaris® LM3S6911 Evaluation Kit provides the hardware and software tools to speed

development of powerful, network-connected devices. Ask your Luminary Micro distributor for part number EKK-LM3S6911 (ARM RealView® MDK tools), EKI-LM3S6911 (IAR Embedded Workbench® tools), EKC-LM3S6911 (CodeSourcery Sourcery G++ tools), or EKT-LM3S6911 (Code Red Technologies Code Suite tools). See the Luminary Micro web site for the latest tools available.



Luminary Micro, Inc. • 108 Wild Basin, Suite 350 • Austin, TX 78746  
Main: +1-512-279-8800 • Fax: +1-512-279-8879 • <http://www.luminarymicro.com>

Copyright © 2007-2008 Luminary Micro, Inc. All rights reserved. Stellaris, Luminary Micro, and the Luminary Micro logo are registered trademarks of Luminary Micro, Inc. or its subsidiaries in the United States and other countries. ARM and Thumb are registered trademarks and Cortex is a trademark of ARM Limited. Other names and brands may be claimed as the property of others.

PB-LM3S6911-01

