

Maxi free-standing Beacons / EvoSIGNAL

Maxi TwinLIGHT 12/24VAC/DC YE



| | |
|------------------|-----------------------|
| Part No.: | 262.310.70 |
| Series: | EvoSIGNAL Maxi |



MECHANICAL DATA

| | |
|------------------------------|-----------------------------|
| Height | 173 mm |
| Diameter | 120 mm |
| Materials | PC PC/ABS |
| Dome colour | Yellow |
| Housing colour | Grey |
| Protection category | IP66 |
| Connection | Push-in terminal |
| cross-sectional area minimum | 0,25mm ² / 24AWG |
| cross-sectional area maximum | 1,50mm ² / 16AWG |
| Working temperature minimum | -30°C |
| Working temperature maximum | +60°C |
| Weight with packaging | 498 g |
| Product weight | 398 g |

ELECTRICAL DATA

| | |
|-----------------------------|--------------------|
| Operating voltage | 12V 24V |
| Operating voltage type | AC/DC |
| Operating voltage frequency | 50Hz |
| Operating voltage tolerance | +/- 10% |
| Rated operational voltage | 24 VDC |
| Rated operational current | 700 mA |
| Rated inrush current | <1800 mA |
| Protection class | Protection class 2 |
| Pollution degree | 3 |
| Overvoltage category | III |

OPTICAL DATA

| | |
|------------------------------|---------------------------------|
| Light source | LED |
| Light colour | Yellow |
| Optical signal image | Blink Permanent TwinLight |
| Blink frequency (Hz) | 1 Hz |
| Service life optical | 50,000 h minimum |
| Pulse- & pause Duration [ms] | 484ON, 480OFF |

APPROVAL DATA


| | |
|------------------|-----|
| Conforms with CE | Yes |
|------------------|-----|

! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

Maxi free-standing Beacons / EvoSIGNAL
Maxi TwinLIGHT 12/24VAC/DC YE

| | |
|-----------------------------|---------|
| WEEE | Yes |
| Conform with ATEX-directive | No |
| Conforms with CCC | No |
| Conforms with UL | cULus |
| UL Type Rating | Type 12 |
| Conforms with FCC | No |
| Conforms with IC | No |
| EAC certificate available | Yes |
| Conforms with UKCA | WERMA |
| Conforms with AS-I | No |
| ICAO Certification | No |
| Conforms with GL | No |
| Conforms with RoHS CN | No |
| Conforms with VdS | No |

DRAWING



! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.