

KERN 573-46

All-rounder e.g. as precision balance in the laboratory or in harsh industrial applications



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	10 h
Input voltage:	100V-230V
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

Services (optional)

DAkKS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 340 x 220 mm
Gross weight:	4,600 kg
Net weight:	2,700 kg
Shipping method:	Parcel service

Construction

Casing material:	Cast aluminium alloys
Dimensions housing (WxDxH):	180 x 310 x 90 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	160 x 200 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readability [d]:	100 mg
Recommended adjusting weight:	6 kg (F1)
Repeatability:	100 mg
Resolution:	65000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	2 h
Weighing capacity [Max]:	6,500 kg
Weighing system:	Strain gauge
Weighing units:	g kg

Display

Display digit height (large):	1,800 cm
-------------------------------	----------

Counting

Counting resolution:	65000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g

Functions

Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes