

Suitable for use with memory card slot

Power Switch for Memory Card Slot

BD6524HFV



●Description

Power switch for memory card Slot (BD6524HFV) is a high side switch IC having one circuit of N-channel Power MOS FET. The switch realizes 200mΩ (Typ.) ON resistance. Operations from low input voltage ($V_{IN} \geq 3.0V$) can be made for use for various switch applications.

The switch turns on slowly by the built-in charge pump, therefore, it is possible to reduce inrush current at switch on. There is no parasitic diode between the drain and the source, reverse current flow at switch off is prevented. Further, it has a discharge circuit that discharges electric charge from capacitive load at switch off.

The BD6524HFV is available in a space-saving HVSO6 package.

●Features

- 1) Low on resistance (200mΩ, Typ.) N-MOS switch built in
- 2) Maximum output current : 500mA
- 3) Soft start circuit
- 4) Under voltage lockout (UVLO) circuit
- 5) Discharge circuit built in : operations at switch off, UVLO
- 6) Reverse current flow blocking at switch off

●Applications

Memory card slots of notebook PC, digital still camera, portable music player, compact portable devices such as PDA and so forth

●Absolute Maximum Ratings

Parameter	Symbol	Rating	Unit
Supply Voltage	V_{IN}	-0.3 to 6.0	V
Control input voltage	V_{EN}	-0.3 to $V_{IN} + 0.3$	V
Switch output voltage	V_{OUT}	-0.3 to 6.0	V
Storage temperature	T_{STG}	-55 to 150	°C
Power dissipation	P_d	510 *1	mW

*1 Derating : 4.08mW/°C for operation above $T_a = 25^\circ C$.

* This product is not designed for protection against radioactive rays.

* Operation is not guaranteed.

●Operation conditions

Parameter	Symbol	Limit	Unit
Supply voltage	V_{IN}	3.0 to 5.5	V
Operating Temperature	T_{OPR}	-25 to 75	°C
Switch current	I_{OUT}	500	mA

●Electrical characteristics

Unless otherwise specified, $T_a = 25^\circ\text{C}$, $V_{IN} = 5\text{V}$,

Parameter	Symbol	Limit			Unit	Condition
		Min.	Typ.	Max.		
Operating current	I_{DD}	-	50	75	μA	$V_{EN} = 5\text{V}$, $V_{OUT} = \text{Open}$
Standby current	I_{STB}	-	0.1	1	μA	$V_{EN} = 0\text{V}$, $V_{OUT} = \text{Open}$
EN input voltage	V_{ENH}	-	-	2.5	V	High level input voltage
	V_{ENL}	0.7	-	-	V	Low level input voltage
EN input leak current	I_{EN}	-1	0.01	1	μA	
Switch on resistance	R_{ON}	-	200	255	$\text{m}\Omega$	$V_{IN} = 5\text{V}$
		-	250	335	$\text{m}\Omega$	$V_{IN} = 3.3\text{V}$
Switch leak current	I_{LEAK}	-	-	10	μA	At switch OFF
Switch rise time	T_{ON1}	-	0.4	0.8	ms	$R_L = 10\ \Omega$. Refer to the timing diagram in Fig. 2.
Switch rise delay time	T_{ON2}	-	0.5	1.0	ms	$R_L = 10\ \Omega$. Refer to the timing diagram in Fig. 2.
Switch fall time	T_{OFF1}	-	1	2	μs	$R_L = 10\ \Omega$. Refer to the timing diagram in Fig. 2.
Switch fall delay time	T_{OFF2}	-	2	4	μs	$R_L = 10\ \Omega$. Refer to the timing diagram in Fig. 2.
UVLO threshold voltage	V_{UVLO}	1.9	2.2	2.5	V	V_{IN} increasing
		1.8	2.1	2.4	V	V_{IN} decreasing
Discharge resistance	R_{DISC}	-	200	350	Ω	$V_{EN} = 0\text{V}$, $I_L = 1\text{mA}$
Discharge current	I_{DISC}	0.8	1.8	-	mA	$V_{EN} = 0\text{V}$ $V_{IN} = V_{OUT} = 1.8\text{V}$

●Measurement circuit




Fig.1 Measurement circuit

●Timing diagram




Fig.2 Timing diagram

● Typical characteristics




Fig.3 Operating current




Fig.4 Standby current




Fig.5 EN threshold voltage (High level input voltage)




Fig.6 EN threshold voltage (Low level input voltage)




Fig.7 Switch on resistance




Fig.8 Switch rise time




Fig.9 Switch rise delay time




Fig.10 Switch fall time




Fig.11 Switch fall delay time




Fig.12 UVLO threshold voltage




Fig.13 Discharge resistance




Fig.14 Operating current




Fig.15 EN threshold voltage




Fig.16 Switch on resistance




Fig.17 Switch rise time




Fig.18 Switch fall time




Fig.19 Discharge resistance

● Waveform data




Fig.20 Switch rise time




Fig.21 Switch fall time




Fig.22 Switch rise time




Fig.23 Switch fall time




Fig.24 Inrush current




Fig.25 Inrush current




Fig.26 UVLO
CL = 10uF




Fig.27 UVLO
CL = 1uF

●Block diagram




Fig.28 Pin configuration




Fig.29 Block diagram

●Pin description

Pin No.	Symbol	Pin Function
1	VIN	Switch input pin.
2		At use, connect each pin outside.
3	EN	Switch control input pin (hysteresis input) Switch ON at High.
4	GND	Ground
5	VOUT	Switch output pin
6		At use, connect each pin outside.

●I/O circuit




Fig.30 I/O circuit

● Functional description

1. Input / output

VIN pin and VOUT pin are connected to the drain and the source of N-MOS switch respectively. And the VIN pin is used also as power source input to internal control circuit.

When EN input is set to High level and the switch is turned on, VIN pin and VOUT pin are connected by a 200mΩ switch. In a normal condition, current flows from VIN to VOUT. If voltage of VOUT is higher than VIN, current flows from VOUT to VIN, since the switch is bidirectional. There is not a parasitic diode between the drain and the source, it is possible to prevent current from flowing reversely from VOUT pin to VIN pin when the switch is disabled.

2. Discharge circuit

When the switch between the VIN and the VOUT is OFF, the 200Ω(Typ.) discharge switch between VOUT and GND turns on. By turning on this switch, electric charge at capacitive load is discharged.

3. Under voltage lockout (UVLO)

The UVLO circuit monitors the voltage of the VIN pin, when the EN input is active. UVLO circuit prevents the switch from turning on until the V_{IN} exceeds 2.2V(Typ.). If the V_{IN} drops below 2.1V(Typ.) while the switch turns on, then UVLO shuts off the switch.

While the switch between the VIN pin and VOUT pin is OFF owing to UVLO operations, the switch of the discharge circuit turns on. However, when the voltage of VIN declines extremely, then the VOUT pin becomes Hi-Z.




Fig.31 Operation timing

● Typical application circuit




Fig.32 Typical application circuit

●Cautions on use

(1) Absolute Maximum Ratings

An excess in the absolute maximum ratings, such as supply voltage, temperature range of operating conditions, etc., can break down devices, thus making impossible to identify breaking mode such as a short circuit or an open circuit. If any special mode exceeding the absolute maximum ratings is assumed, consideration should be given to take physical safety measures including the use of fuses, etc.

(2) Operating conditions

These conditions represent a range within which characteristics can be provided approximately as expected. The electrical characteristics are guaranteed under the conditions of each parameter.

(3) Reverse connection of power supply connector

The reverse connection of power supply connector can break down ICs. Take protective measures against the breakdown due to the reverse connection, such as mounting an external diode between the power supply and the IC's power supply terminal.

(4) Power supply line

Design PCB pattern to provide low impedance for the wiring between the power supply and the GND lines. In this regard, for the digital block power supply and the analog block power supply, even though these power supplies have the same level of potential, separate the power supply pattern for the digital block from that for the analog block, thus suppressing the diffraction of digital noises to the analog block power supply resulting from impedance common to the wiring patterns. For the GND line, give consideration to design the patterns in a similar manner.

Furthermore, for all power supply terminals to ICs, mount a capacitor between the power supply and the GND terminal. At the same time, in order to use an electrolytic capacitor, thoroughly check to be sure the characteristics of the capacitor to be used present no problem including the occurrence of capacity dropout at a low temperature, thus determining the constant.

(5) GND voltage

Make setting of the potential of the GND terminal so that it will be maintained at the minimum in any operating state. Furthermore, check to be sure no terminals are at a potential lower than the GND voltage including an actual electric transient.

(6) Short circuit between terminals and erroneous mounting

In order to mount ICs on a set PCB, pay thorough attention to the direction and offset of the ICs. Erroneous mounting can break down the ICs. Furthermore, if a short circuit occurs due to foreign matters entering between terminals or between the terminal and the power supply or the GND terminal, the ICs can break down.

(7) Operation in strong electromagnetic field

Be noted that using ICs in the strong electromagnetic field can malfunction them.

(8) Inspection with set PCB

On the inspection with the set PCB, if a capacitor is connected to a low-impedance IC terminal, the IC can suffer stress. Therefore, be sure to discharge from the set PCB by each process. Furthermore, in order to mount or dismount the set PCB to/from the jig for the inspection process, be sure to turn OFF the power supply and then mount the set PCB to the jig. After the completion of the inspection, be sure to turn OFF the power supply and then dismount it from the jig. In addition, for protection against static electricity, establish a ground for the assembly process and pay thorough attention to the transportation and the storage of the set PCB.

(9) Input terminals

In terms of the construction of IC, parasitic elements are inevitably formed in relation to potential. The operation of the parasitic element can cause interference with circuit operation, thus resulting in a malfunction and then breakdown of the input terminal. Therefore, pay thorough attention not to handle the input terminals, such as to apply to the input terminals a voltage lower than the GND respectively, so that any parasitic element will operate. Furthermore, do not apply a voltage to the input terminals when no power supply voltage is applied to the IC. In addition, even if the power supply voltage is applied, apply to the input terminals a voltage lower than the power supply voltage or within the guaranteed value of electrical characteristics.

(10) Ground wiring pattern

If small-signal GND and large-current GND are provided, it will be recommended to separate the large-current GND pattern from the small-signal GND pattern and establish a single ground at the reference point of the set PCB so that resistance to the wiring pattern and voltage fluctuations due to a large current will cause no fluctuations in voltages of the small-signal GND. Pay attention not to cause fluctuations in the GND wiring pattern of external parts as well.


(11) External capacitor

In order to use a ceramic capacitor as the external capacitor, determine the constant with consideration given to a degradation in the nominal capacitance due to DC bias and changes in the capacitance due to temperature, etc.

(12) Thermal design

Perform thermal design in which there are adequate margins by taking into account the power dissipation (Pd) in actual states of use.

●Product Designation



HVSO6

<Dimension>

(Unit:mm)

<Tape and Reel information>

Tape	Embossed carrier tape
Quantity	3000pcs
Direction of feed	TR (The direction is the 1pin of product is at the upper light when you hold reel on the left hand and you pull out the tape on the right hand)

※When you order , please order in times the amount of package quantity.

- The contents described herein are correct as of April, 2005
- The contents described herein are subject to change without notice. For updates of the latest information, please contact and confirm with ROHM CO.,LTD.
- Any part of this application note must not be duplicated or copied without our permission.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams and information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by ROHM CO., LTD. is granted to any such buyer.
- The products described herein utilize silicon as the main material.
- The products described herein are not designed to be X ray proof.

The products listed in this catalog are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys). Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Excellence in Electronics



ROHM CO., LTD.

21, Saiin Mizosaki-cho, Ukyo-ku, Kyoto
615-8585, Japan
TEL: (075)311-2121 FAX: (075)315-0172
URL <http://www.rohm.com>

Published by
LSI Application Engineering Group

Contact us for further information about the products.

- Atlanta U.S.A. / ROHM ELECTRONICS ATLANTA SALES OFFICE
(DIVISION OF ROHM ELE. U.S.A.,LLC)
TEL: +1(770)754-5972 FAX: +1(770)754-0691
- Dallas U.S.A. / ROHM ELECTRONICS DALLAS SALES OFFICE
(DIVISION OF ROHM ELE. U.S.A.,LLC)
TEL: +1(972)312-8818 FAX: +1(972)312-0330
- San Diego U.S.A. / ROHM ELECTRONICS SAN DIEGO SALES OFFICE
(DIVISION OF ROHM ELE. U.S.A.,LLC)
TEL: +1(858)625-3630 FAX: +1(858)625-3670
- Germany / ROHM ELECTRONICS GMBH (GERMANY)
TEL: +49(2154)9210 FAX: +49(2154)921400
- United Kingdom / ROHM ELECTRONICS GMBH (UK)
TEL: +44(0)1908-306700 FAX: +44(0)1908-235788
- France / ROHM ELECTRONICS GMBH (FRANCE)
TEL: +33(1)41 23 14 00 FAX: +33(1)4123-1430
- Hong Kong China / ROHM ELECTRONICS (H.K.) CO., LTD.
TEL: +852(2)740282 FAX: +852(2)375-8371
- Shanghai China / ROHM ELECTRONICS (SHANGHAI) CO., LTD.
TEL: +86(21)6279-2727 FAX: +86(21)6247-2066

- Dalian China / ROHM ELECTRONICS TRADING (DALIAN) CO., LTD.
TEL: +86(411)8230-8549 FAX: +86(411)8230-8537
- Beijing China / BEIJING REPRESENTATIVE OFFICE
TEL: +86(10)6525-2483 FAX: +86(10)6525-2489
- Taiwan / ROHM ELECTRONICS TAIWAN CO., LTD.
TEL: +886(2)2500-6956 FAX: +886(2)2503-2869
- Korea / ROHM ELECTRONICS KOREA CORPORATION
TEL: +82(2)8182-7000 FAX: +82(2)8182-715
- Singapore / ROHM ELECTRONICS ASIA PTE. LTD. (RES/REI)
TEL: +65-6332-2322 FAX: +65-6332-5662
- Malaysia / ROHM ELECTRONICS (MALAYSIA) SDN. BHD.
TEL: +60(3)7958-8355 FAX: +60(3)7958-8377
- Philippines / ROHM ELECTRONICS (PHILIPPINES) SALES CORPORATION
TEL: +63(2)807-6872 FAX: +63(2)809-1422
- Thailand / ROHM ELECTRONICS (THAILAND) CO., LTD.
TEL: +66(2)254-4890 FAX: +66(2)256-6334

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

It is our top priority to supply products with the utmost quality and reliability. However, there is always a chance of failure due to unexpected factors. Therefore, please take into account the derating characteristics and allow for sufficient safety features, such as extra margin, anti-flammability, and fail-safe measures when designing in order to prevent possible accidents that may result in bodily harm or fire caused by component failure. ROHM cannot be held responsible for any damages arising from the use of the products under conditions out of the range of the specifications or due to non-compliance with the NOTES specified in this catalog.

Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact your nearest sales office.

ROHM Customer Support System

THE AMERICAS / EUROPE / ASIA / JAPAN

www.rohm.com

Contact us : webmaster@rohm.co.jp