

# KERN ABJ120-4NM



The bestseller in analytical balances, with high-quality single-cell weighing system, also with EC type approval [M]



Minimum piece weight at piece counting (Normal): 10 mg

Reference weight: yes

## Functions

Counting function: yes

Function to save totals: yes

Percentage determination: yes

Standby function: yes

Weighing with tolerance range: yes

## Environmental conditions

Maximum humidity: 85 %

Maximum operating temperature: 30 °C

Minimum ambient temperature: 10 °C

Minimum humidity: 20 %

## Power supply

Input voltage: 110 V - 230 V AC

Mains adapter: Mains adapter external

Mains adapter/adapter included: EURO CH AUS UK US

## Services (optional)

DAkkS Certificate: 963-101

## Category

Brand: KERN

Category: Balances

Product Group: Analytical balance

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 390 x 563 x 515 mm

Gross weight: 9,207 kg

Net weight: 6,271 kg

Shipping method: Parcel service

## Construction

Dimensions draft shield (WxDxH): 201 x 220 x 256 mm

Dimensions housing (WxDxH): 210 x 340 x 350 mm

Level indicator: yes

Material weighing plate: stainless steel

Revolving screw feet: yes

Weighing space (WxDxH): 174 x 162 x 227 mm

Weighing surface (d): 91

## Measuring system

Adjustment options: Internal calibration (manual)  
Internal calibration (auto)

Linearity: 0,300 mg

Minimum weight (USP): 400 mg

Readability [d]: 0,100 mg

Repeatability: 0,200 mg

Resolution: 1.200.000

Stabilisation time under laboratory conditions: 3 s

Warm up time: 8 h

Weighing capacity [Max]: 120 g

Weighing units: g ct mg

## Display

Display digit height (large): 1,400 cm

## Technical data about verification

Verification class: I

## Counting

Counting resolution: 120000

Minimum piece weight at piece counting (Laboratory): 1 mg

# KERN ABJ120-4NM




The bestseller in analytical balances, with high-quality single-cell weighing system, also with EC type approval [M]

## Piktogramme

### STANDARD



### OPTION



### FACTORY

