


KERN ALJ250-4AM



Analytical balance range with large weighing ranges, intuitive graphics display and extensive recipe database



Technical data about verification

Minimum load [Min]:	10 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	I
Verification value [e]:	1 mg

Counting

Counting resolution:	250000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg
Reference weight:	yes

Functions

Capacity display:	yes
Counting function:	yes
Density determination function:	yes
Dispensing function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Input voltage:	country-dependent
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH AUS UK US

Services (optional)

DAkkS Certificate:	963-101
Verification:	965-201

Category

Brand:	KERN
Category:	Balances
Product Group:	Analytical balance

Measuring system

Adjustment options:	Internal calibration (auto)
Linearity:	0,300 mg
Minimum weight (USP):	200 mg
Readability [d]:	0,100 mg
Repeatability:	0,100 mg
Resolution:	2.500.000
Stabilisation time under laboratory conditions:	4 s
Warm up time:	8 h
Weighing capacity [Max]:	250 g
Weighing system:	Force compensation
Weighing units:	tl (HK) g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) gn mg ozt

Display

Display digit height (large):	1,500 cm
Display digit height (small):	4 mm

KERN ALJ250-4AM



Analytical balance range with large weighing ranges, intuitive graphics display and extensive recipe database

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 515 x 615 mm
Gross weight:	9 kg
Net weight:	6,500 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions draft shield (WxDxH):	172 x 185 x 245 mm
Dimensions housing (WxDxH):	210 x 340 x 330 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	210 x 340 x 330 mm
Revolving screw feet:	yes
Weighing space (WxDxH):	160 x 170 x 225 mm
Weighing surface (d):	80

Piktogramme

STANDARD



OPTION

