

KERN CDS15K0.05

Easy to use industrial counting scale for heavy loads, counting resolution up to 300,000 points



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

DAkkS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	520 x 390 x 150 mm
Gross weight:	9,800 kg
Net weight:	7,500 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	2 m
Dimensions housing (WxDxH):	225 x 115 x 60 mm
Dimensions of display device (WxDxH):	225 x 115 x 60 mm
Dimensions of weighing plate (WxDxH):	308 x 318 x 75 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	308 x 318 mm

Measuring system

Adjustment options:	External calibration
Linearity:	250 mg
Readability [d]:	50 mg
Recommended adjusting weight:	15 kg (F1)
Repeatability:	100 mg
Resolution:	300000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	g

Display

Display digit height (large):	1,800 cm
-------------------------------	----------

Counting

Counting resolution:	300000
Minimum piece weight at piece counting (Laboratory):	50 mg
Minimum piece weight at piece counting (Normal):	500 mg

Functions

Counting function:	yes
Standby function:	yes

KERN CDS 15K0.05

Easy to use industrial counting scale for heavy loads, counting resolution up to 300,000 points



Piktogramme

STANDARD



OPTION

