



The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

Click [here](#) for the 3D model.

Dimensions	
D	11mm MAX
T	6mm MAX
S	10mm MAX
LL	5mm +/-1mm
F	0.6mm +/-0.1mm
A	4mm MAX

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	C700KJN SFTY X1-440 Y1-400
Style	Radial Disc
RoHS	Yes
Termination	Tin
Failure Rate	N/A
Qualifications	UL, CSA, TUV
AEC-Q200	No

Specifications	
Capacitance	47 pF
Capacitance Tolerance	5%
Voltage AC	440 VAC (X1), 400 VAC (Y1)
Dielectric Withstanding Voltage	4000 VDC
Temperature Range	-40/+125°C
Temperature Coefficient	SL
Dissipation Factor	0.3% 1MHz 5.0Vrms
Insulation Resistance	10 GOhms
Safety Class	X1/Y1