

KERN IFB 10K-4L

High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg



Measuring system

Adjustment options:	External calibration
Linearity:	1,500 g
Load cell connection:	6-wire
Readability [d]:	500 mg
Recommended adjusting weight:	15 kg (F2)
Repeatability:	500 mg
Resolution:	30000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	2 h
Weighing capacity [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	g lb lb:oz Hj. tJ kg

Display

Display digit height (large):	5,200 cm
-------------------------------	----------

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	500 mg
Minimum piece weight at piece counting (Normal):	5 g

Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Battery:	no battery
Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 800 x 240 mm
Gross weight:	12 kg
Net weight:	7,500 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Casing material:	Plastic
Dimensions of display device (WxDxH):	250 x 160 x 58 mm
Dimensions of weighing plate (WxDxH):	400 x 300 x 128 mm
of stand:	60 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	560 x 300 x 490 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	400 x 300 mm


KERN IFB10K-4L



High-resolution scale in heavy version with EC type approval [M], now also up to [Max] 600 kg

Piktogramme

STANDARD



OPTION



FACTORY

